Pass and Seymour

Three Pole Three Phase AC Manual Controller

Part No. 7803MD

Three Pole, Three Phase AC Manual Motor Controller, suitable as Motor Disconnect - 10KA @ 600VAC, 30A max. Class J Fuse.

Features & Benefits

- High Horsepower rating of 20HP
- Constructed of glass-reinforced thermoplastic
- Heavy-duty zinc-plated steel strap, two brass rivets secure strap to housing
- For covering patents, see www.legrand.us/patents.
- Gull-wing shaped brass terminal pressure clamps
- UL508 and cULus Listing of individual device and assembled device within enclosure
- External screw-pressure-plate back and side wire terminal screws unstaked for use with ring terminals
- For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click here.

Specifications

General Info

Product Line	Pass & Seymour	Country Of Origin	Mexico
Standard	CSA Listed, UL Listed		

Dimensions

Product Width US	1.825 in	Product Depth US	1.753 in
Product Height US	3.67 in		

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes

Technical Information

Operating Cycles	50000	Actuator	Toggle
Connection	Side & Back Wired	Amperage	30 A
Voltage	600 V	Environmental Conditions	UL94 V2