adorne Collection

adorne® sofTap Tru-Universal Dimmer with Magnesium Wall Plate, Magnesium

Part No. ADTP703TUM4WP

Turn lights on/off, or dim, with just a soft tap of a finger, thanks to inventive micro-movement technology. Plus, as a Tru-Universal Dimmer, it works with virtually any 120V dimmable bulb or fixture, adjusting to the precise light level you want, without the flicker. Coordinating screwless Wall Plate included, for a sleek and contemporary aesthetic.

Features & Benefits

For complete installation, device must be paired with an adorne® screwless Wall Plate (not included). Available in a range of contemporary colors and stunning finishes.

Installs in 15 minutes or less, fitting into an existing electrical box; neutral wire required

Works with virtually any 120V dimmable bulb or fixture (excludes 0-10V)

Self-calibrates when you select your fixture's lighting type, automatically setting the appropriate minimum voltage to eliminate flicker and poor performance

Constant memory feature returns lights to their previous level when turning back on or after a power outage

Offers installation flexibility, working in both single-pole and 3-way applications

Usable in both single-pole and 3-way applications

More color options available to fit any style, including finishes to match current hardware and lighting trends

Specifications

General Info

Product Line	Pass & Seymour	Color	Magnesium
Finish	Frosted	UPC Number	785007158502
Country Of Origin	China	Features	Indicator Lights
Switch Type	sofTap	Number of Switches	1
Device Front Face Size	Full-Size	Device Backbody Size	Plus-Size
Application Sector	Residential	Standard	cULus
Warranty Type	Limited Lifetime Warranty	Type	Dimmer

Dimensions

Product Width US	3.45 in	Product Depth US	1.79 in
Product Height US	5.13 in		

Technical Information

Compatibility	EFL: 5.5A, Halogen & ELV: 700W, Incandescent, LED/CFL: 450W (not compatible with 0-10V LED drivers), MLV: 500VA	Electrical Rating	120V 1100W (Halogen), 120V 1600VA (MLV), 120V 16A (Fluorescent), 120V 2000W (Incandescent), 120V 450W (CFL), 120V 450W (LED), 120V 5A (Fan Control), 120V 700W (ELV), 120V 8A (EFL)
Connection	Screw Terminals	Number of Gangs	1
Bulb Compatibility	CFL, Fluorescent, Halogen, HID, Incandescent, LED, Universal, Xenon	Number of Poles	Single Pole 3-Way
Wire Size	#14 - #10 AWG	Requires Neutral Wire	Yes
Indoor/Outdoor	Indoor	Wattage	700 W
Mounting Type	Box	Connection Type	Internal Pressure Plates