Pass and Seymour

Discontinued - Titan Series Fluorescent 3 Wire Dimmer, White

Part No. CD3FB103P277W

Ganging conventional dimmers used to require costly, customized wall plates that couldn't be ordered until a configuration was finalized. Titan® Series Dimmers change all that. Unlike the others, Titan Dimmers are a complete solution that saves time and money and offers end-users a superior, more convenient, better-looking multi-gang installation.

Features & Benefits

- For use with 3 wire 120V and 277V fluorescent dimming ballasts.
- Labeling system
- Shipped with protective film
- Superior ratings with a minimum of derating when ganged
- Available in single pole slide-to-OFF and single pole/3-way preset models
- Exclusive adaptor kit to install other Decorator opening devices under the Titan wall plate system
- Field configurable wall plate system
- Adjustable low end output voltage
- Rugged construction
- Simple to plan the rough-in
- Attractive European styling. Eye-catching packaging
- Blank center plate included

Specifications

General Info

Product Line	Pass & Seymour	Color	White
Country Of Origin	China	Application Sector	Commercial
Standard	cULus, California Title 24 Compliant	Type	Dimmer

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes

Technical Information

Operating Cycles	100	Frequency Rating	60 Hz
Amperage	10 A	Voltage	277.0 V
Load	Up to rating of device (including de-rating)	Environmental Conditions	Non-Condensing Humidity: Less than 95%