Pass and Seymour

# Discontinued - Titan Series Fluorescent 2 Wire Dimmer, Ivory

Part No. CDFB16I

## Features & Benefits

- For use with 2 wire 120V and 277V fluorescent dimming ballasts.
- Field configurable wall plate system.
- Labeling system.
- Adjustable low end output voltage.
- Shipped with protective film.
- Rugged construction.
- Superior ratings with a minimum of derating when ganged.
- Simple to plan the rough-in.
- Available in single pole slide-to-OFF and single pole/3-way preset models.
- Attractive European styling.
- Eye-catching packaging.
- Exclusive adaptor kit to install other Decorator opening devices under the Titan: wall plate system. (See Page N-29.)
- Blank center plate included.
- For covering patents, see www.legrand.us/patents.

## Specifications

### General Info

| | | | |
|---|---|---|---|
| Product Line | Pass & Seymour | Color | Ivory |
| UPC Number | 785007302745 | Country Of Origin | China |
| Application Sector | Commercial | Standard | cULus, California Title 24 Compliant |
| Type | Dimmer | | |

### Listing Agencies / 3rd Party Agencies

| | |
|---|---|
| cULus Listed | Yes |

## Technical Information

| | | | |
|---|---|---|---|
| Operating Cycles | 100 | Amperage | 16 A |
| Number of Poles | Single Pole | Environmental Conditions | Non-Condensing Humidity: Less than 95% |