



adorne Collection
adorne® Paddle Fan Speed Control Switch, White, with Microban®
Part No. AAFN4S16AW4

Upgrade your fan's speed control and stop using those clunky, hard-to-reach fan cords. Now you can adjust the speed of your ceiling fan quietly, and in style, thanks to the adorne Collection.



This fan speed control switch features four speed settings and a sleek on/off switch. Use on its own to control a fan from one location, or pair with a 3-way switch and conveniently control a single fan from two locations.

This switch* features enduring Microban® antimicrobial technology that works to reduce the growth of bacteria, around the clock, for the lifespan of the product.

* Existing inventory of switches, dimmers and plastic wall plates from the adorne® Collection at some partner locations may not yet include Microban® protection. To confirm that a specific Legrand product is protected with Microban®, check that the exterior of the product packaging includes a green dot or a "Protected with Microban" label.

Made exclusively for use with screwless Wall Plates from the adorne® Collection, sold separately.

No antimicrobial efficacy claims are being made or are valid with respect to products sold in Canada.

Features & Benefits

Helps fight the growth of stain and odor-causing bacteria through the invisible and continuous product protection of Microban® antimicrobial technology

For complete installation, device must be paired with an adorne® screwless Wall Plate (not included). Available in a range of contemporary colors and stunning finishes.

Installs in 15 minutes or less, fitting into an existing electrical box. No new wiring required for typical installation.

Features easy on/off control, as well as four speed settings.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

Specifications

General Info

Product Line	Pass & Seymour	Replaced by Part Number	
Color	White	Country Of Origin	China
Features	Antimicrobial Protection, Fan Control	Switch Type	Paddle

Number of Switches	1	Standard	cULus
--------------------	---	----------	-------

Warranty Type	Limited Lifetime Warranty
---------------	---------------------------

Dimensions

Product Width US	1.85 in	Product Depth US	1.77 in
------------------	---------	------------------	---------

Product Height US	2.66 in
-------------------	---------

Technical Information

Actuator	Paddle	Connection	Screw Terminals
----------	--------	------------	-----------------

Number of Gangs	1	Amperage	1.6 A
-----------------	---	----------	-------

Number of Poles	3-Way, Single Pole	Wattage	1100 W
-----------------	--------------------	---------	--------

Mounting Type	Box	Speed Range	4-Speed
---------------	-----	-------------	---------

Voltage	120.0 V	Connection Type	Internal Pressure Plates
---------	---------	-----------------	--------------------------
