Pass and Seymour
Commerical Specification Grade Switches, White
Part No. CS15AC1W

Commercial 1-Pole Switch, Side-Wire, 15A 120/277V.

Features & Benefits

One-piece brass alloy contact arm for reliable electrical performance.

One-piece steel strap with integral ground is plated for corrosion resistance.

High strength thermoplastic polycarbonate toggle resists breaking and chipping under heavy abuse.

Heavy-duty toggle bumpers for smooth and quiet operation.

Back body made of glass-reinforced nylon. Locking support provides resistance to face and back body separation.

Available with side wire or external screw-pressure-plate back and side wire models capable of accepting #14 - #10 AWG copper or copper-clad wire.

Cam designed for fast make with positive break action to minimize arcing and prolong switch life.

Oversized silver alloy contacts for longer dependable switch life.

Tri-drive terminal and mounting screws.

For covering patents, see www.legrand.us/patents.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click here.

Specifications

General Info

Product Line	Pass & Seymour	Color	White
Country Of Origin	Mexico	Application Sector	Commercial
Standard	UL 498/20		

Dimensions

Product Width US	1.32 in	Product Depth US	1.073 in

Product Height US	3.281 in

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140597	cULus Listed	Yes

Technical Information

Actuator	Toggle	Contact Rating	15Amp, 120/277Vac
Amperage	15 A	Action	Single pole
Number of Poles	Single Pole	Voltage	120.0 V