Cablofil
**4" Itray Aluminum Straight Sections**
Part No. P300036

The aluminum I-beam design of ITray is perfect for industrial installations with large diameter cables in long span situations, minimizing total tray width and creating a smooth transition between straight sections and fittings. A structural offset in the sidewall creates strong, mid-span splices that need fewer supports. Each splice snaps in place and stays without holding, Additionally, only four bolts are needed for each splice reducing hardware needs by 50%. These features allow Itray to be installed up to 30% faster than standard tray.

## Features & Benefits

Material: Aluminum Alloy 6063-T6

Finish: Plain

Bottom: Ldr: 1'' wide I rung SB: Flat Sheet over 12'' Rung Spacing. SC:Solid Corrugated VC: Vented Corrugated

Construction: Welded

Tray Design: Tray construction and markings are per the latest edition of NEMA Standards Publication VE1, CSA C22.2 No. 126.

Tray Grounding Capability: Classified as an equipment grounding conductor per NEC 392.60.

## Specifications

### General Info

| | | | |
|---|---|---|---|
| Product Line | Cablofil | Finish | Aluminum |
| UPC Number | 800388059016 | Country Of Origin | Mexico |
| Application Sector | Commercial, Industrial | Type | Cable Tray |

### Dimensions

| | | | |
|---|---|---|---|
| Product Width US | 37.5 in | Product Weight US | 21.75 lb |
| Product Volume US | 10.755 cu ft | Product Depth US | 120.0 in |
| Product Height US | 4.13 in | | |

### Buy American Act Compliance

| | |
|---|---|
| BAA | Yes |