




radiant Collection  
 radiant® Smart Switch with Netatmo, White  
 Part No. WNRL10WH



Control lights at the wall with the smooth paddle action of this smart switch, or use the intuitive app. Pair this switch with a Wireless Smart Switch with Netatmo to gain easy 3-way control. Smart Lighting lets you set the exact lighting you need, from anywhere, adding safety and convenience to your home. And delivering it all with unprecedented range and reliability, radiant® with Netatmo leverages leading Netatmo technology to provide an ideal solution for larger homes with many smart products. Start with the Smart Gateway to establish a robust and dedicated mesh network, then add smart light switches, smart dimmer light switches and smart outlets to build a solution that perfectly fits a home's unique space and needs. Screwless Wall Plates from the radiant® Collection included.

## Features & Benefits

Smart Gateway REQUIRED.

Controls lights, from anywhere, via smartphones and tablets through the Legrand Home + Control app. Schedule lights to turn on/off automatically, create groups, set scenes, monitor energy usage and more.

Installs easily in place of an existing single-pole switch or dimmer (neutral wire required). For easy 3-way control, pair with a Wireless Smart Switch with Netatmo.

Part of the radiant with Netatmo solution, which flexibly fits a home's unique needs with a variety of supported smart switches, dimmers and outlets (including other wireless switches and dimmers).

Features ultra-reliable performance through a robust and dedicated mesh-network. (Established by the Smart Gateway.)

Compatible with other smart products through Amazon Alexa, Google Assistant and Apple HomeKit, as well as with home automation systems.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

Screwless Wall Plate included. Coordinate with other designer switches and outlets available from the radiant® Collection for a cohesive, sophisticated look

## Specifications

### General Info

|                   |                |                         |                              |
|-------------------|----------------|-------------------------|------------------------------|
| Product Line      | Pass & Seymour | Replaced by Part Number |                              |
| Color             | White          | Finish                  | Matte                        |
| Country Of Origin | China          | Features                | Smart Lighting, With Netatmo |
| Switch Type       | Paddle         | Number of Switches      | 1                            |

---

|            |   |                    |                            |
|------------|---|--------------------|----------------------------|
| Works With | Amazon Alexa, Apple Home Kit,<br>Google Assistant | Application Sector | Commercial,<br>Residential |
|------------|---|--------------------|----------------------------|

---

|               |                         |      |        |
|---------------|-------------------------|------|--------|
| Warranty Type | 1-Year Limited Warranty | Type | Switch |
|---------------|-------------------------|------|--------|

---

### Listing Agencies / 3rd Party Agencies

---

|                     |         |              |     |
|---------------------|---------|--------------|-----|
| cULus ListingNumber | E350248 | cULus Listed | Yes |
|---------------------|---------|--------------|-----|

---

|               |     |  |  |
|---------------|-----|--|--|
| FCC Compliant | Yes |  |  |
|---------------|-----|--|--|

---

### Additional Information

---

|                 |     |   |     |
|-----------------|-----|---|-----|
| RoHS Conformant | Yes | Product Has Potential to Contribute to LEED | Yes |
|-----------------|-----|---|-----|

---

### Technical Information

---

|               |  |          |        |
|---------------|--|----------|--------|
| Compatibility | Amazon Alexa, Apple HomeKit,<br>Google Assistant | Actuator | Paddle |
|---------------|--|----------|--------|

---

|            |       |          |      |
|------------|-------|----------|------|
| Connection | Wired | Amperage | 15 A |
|------------|-------|----------|------|

---

|                 |                                       |               |     |
|-----------------|---------------------------------------|---------------|-----|
| Number of Poles | 3-Way, Multi-Location, Single<br>Pole | Mounting Type | Box |
|-----------------|---------------------------------------|---------------|-----|

---

|         |         |                 |       |
|---------|---------|-----------------|-------|
| Voltage | 120.0 V | Connection Type | Wired |
|---------|---------|-----------------|-------|

---