Pass and Seymour

15A 125V Clock Hanger Recessed Single Receptacle with Smooth Wall Plate, Ivory

Part No. S3713I

Clock Hanger Recessed Receptacle with Smooth Wall Plate 15A, 125V, Gray

Features & Benefits

Single recessed receptacle.	Available in 'TP' series, extra 3/16 inch width and height than Standard size plates: and 'TPJ' series, extra 3/16 inch width and height than Junior-Jumbo size plates.

Specifications

General Info

Product Line	Pass & Seymour	Color	Ivory
Country Of Origin	Mexico	Number of Receptacles	1
Outlet Type	Commercial, Indoor	Application Sector	Residential/Commercial
Standard	UL 498	Type	Outlet

Dimensions

Product Width US	2.74 in	Product Depth US	1.88 in
Product Height US	4.478 in		

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140596	cULus Listed	Yes

Technical Information

Connection	Wire Ground	Number of Wires	3

Amperage	15 A	Number of Poles	Double Pole
Wire Size	4 AWG	Indoor/Outdoor	Indoor
Voltage	125.0 V		