Pass and Seymour

**Combination Openings, 2 Toggle Switch and 2 Duplex Receptacle, Four Gang, 302/304 Stainless Steel**

Part No. SS282

Smooth Metal Wall Plate 2-Gang Toggle 2-Gang Duplex 302/304 Stainless Steel

## Features & Benefits

- Type 302/304 Stainless Steel, non-magnetic: .032''' nominal thickness.
- Brushed finish.
- This alloy contains 18% chromium and 8% nickel for superior resistance to corrosion.
- Recommended for use in food processing plants, dairies, chemical plants, and other industrial, institutional, and commercial applications where corrosive atmospheres exist.
- Standard, Jumbo, and Tandem plates available, as well as special Panel plates up to 5-gangs high and 10-gangs wide.
- Packaged in protective film, with finish-matching screws.
- Variety of special plated finishes.
- Paintable to match plastic plates.
- Can be silk-screened or engraved, and custom punched with over 300 opening styles.

## Specifications

### General Info

| | | | |
|---|---|---|---|
| Product Line | Pass & Seymour | Country Of Origin | United States |
| Application Sector | Residential/Commercial | Standard | CSA |

### Dimensions

| | | | |
|---|---|---|---|
| Product Width US | 8.125 in | Product Depth US | 0.2 in |
| Product Height US | 4.5 in | | |

### Listing Agencies / 3rd Party Agencies

| | | | |
|---|---|---|---|
| CSA Listed | Yes | cULus Listed | Yes |

### Technical Information

| | | | |
|---|---|---|---|
| Cutout | Toggle and Receptacle | Thickness | 0.032 in |
| Number of Gangs | 4 | | |