Pass and Seymour

20A 125V Hard Use Spec-Grade Tamper-Resistant Half-Controlled Plug Load Decorator Duplex Receptacle, Black

Part No. TR5362CHBK

Permanent controlled receptacle marking allows for long-lasting, easy identification of controlled receptacle for end-users. NEMA-approved and compliant with NEC, CA Title 24, and ASHRAE Energy Efficiency Standard 90.1.

Features & Benefits

Can be wired to any number of system-based or stand-alone plug load control solutions.

.032 inch thick, brass, triple-wipe power contacts for lasting retention.

Two drive screws anchor strap to back body and face where abrupt removal torque is strongest.

Strap tabs wrap around face to prevent strap from separating from face and back body.

For covering patents, see www.legrand.us/patents.

Two drive screws anchor strap to back body and face where abrupt removal torque is greatest.

Permanent controlled receptacle markings using abrasion resistant ink.

Tri-drive brass-plated terminal screws. Two back-wire holes for more wiring flexibility.

CH Version Only: Split circuit tab broken at the factory, allowing half of the receptacle to be controlled.

Specifications

General Info

Product Line	Pass & Seymour	Color	Black
UPC Number	785007051278	Country Of Origin	Mexico
Number of Receptacles	2	Outlet Type	Energy Saving On/Off, Tamper-Resistant
Application Sector	Commercial	Warranty Type	1-Year Limited Warranty
Type	Outlet		

Dimensions

Product Width US	1.322 in	Product Depth US	1.13 in
Product Height US	2.635 in		

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140596	cULus Listed	Yes

Technical Information

Amperage	20 A	Number of Poles	Double Pole

Indoor/Outdoor	Indoor