Pass and Seymour

**TradeMaster® LED/CFL/Incandescent Single Pole/3-Way Toggle Slide Dimmer, Preset, Gray**

Part No. TSDCL303PGRY

TradeMaster® Toggle Slide Dimmer is designed for use with compact fuorescent or LED lighting fixtures. This single pole 3-way switch can be used in a two-location layout. The slide can be set to your prefered level and then toggle on and off providing instant repeatablility.

This switch offers dependability and a lifetime warranty.

## Features & Benefits

- Matches appearance of standard Pass and Seymour toggle switch
- Interchangeable face covers are available in seven different colors
- Lifetime warranty
- All models are Single Pole/3-Way capable
- Highest wattage rating

## Specifications

### General Info

| | | | |
|---|---|---|---|
| Product Line | Pass & Seymour | Color | Gray |
| Finish | Matte | UPC Number | 785007215960 |
| Country Of Origin | China | Features | Preset |
| Switch Type | Rocker, Slider | Number of Switches | 1 |
| Application Sector | Residential | Warranty Type | Limited Lifetime Warranty |

### Dimensions

| | | | |
|---|---|---|---|
| Product Width US | 2.5 in | Product Depth US | 1.4 in |
| Product Height US | 4.19 in | | |

### Technical Information

| | | | |
|---|---|---|---|
| Amperage | 2.5 A | Bulb Compatibility | CFL, Incandescent, LED |
| Number of Poles | 3-Way, Single Pole | Wire Size | #14 - #10 AWG |

| | |
|---|---|
| Wattage | 700 W |