NUVO

In-Wall Single Passive 8" Subwoofer

Delivering a stand-out bass response, the In-Wall Single Passive 8" Subwoofer brings a whole new dimension of detailed clarity to music and movies. With a discrete design that allows for space-saving in-wall placement, the NV-SUBIW8 adds a powerful low-frequency impact to smaller home theater or audio installations. Its sealed cabinet is constructed of durable MDF for a distortion-free, superior bass experience. A square magnetic grill is included.

- **Discrete wall-mounted passive single 8" subwoofer ideal for medium sized audio installations**
- **Installation-friendly sealed cabinet design**
- **Pair up with optional NV-SUBAMP200-xx amplifier**
- **Square magnetic grill included**
- **Up to two single subwoofers may be used with optional NV-SUBAMP200-xx amplifier**
- **Lifetime warranty**
- **Space-saving design**

The NV-SUBAMP200 optional matching amplifier offers maximum versatility with rack-mount capability. The pair are designed to integrate with almost any audio system. The NV-SUBAMP200-xx features signal-sensing power activation (optional setting) to automatically turn on the subwoofer when it detects a signal from the receiver. It will return to standby automatically after approximately 15 minutes of no signal. Unfiltered LFE / RCA stereo inputs let you easily connect the amplifier to most modern receivers. The variable crossover and phase controls allow you to match the Subwoofer output with the main speakers for premium performance and sound. Convenient 12V DC trigger inputs and outputs allow the amplifier to be controlled by external devices or control other external items. A three-position EQ switch allows the amplifier output to be tailored to any Nuvo in-ceiling or in-wall passive subwoofers. One or two NV-SUBIW8 subwoofers may be used with one NV-SUBAMP200-xx.

NV-SUBAMP200

Nuvo In-Wall Single Passive 8" Subwoofer

Material
MDF Enclosure with Aluminum Frame and Steel Grill

Color
Black with White Grill

Unit Size

(mm)	347.6 x 347.6 x 106.8
(in)	13.7 x 13.7 x 4.2

Unit Weight

(kg)	5.9
(lbs)	13.01

Shipping

Package Dimensions (mm)	465 x 465 x 260
Package Dimensions (in)	18.3 x 18.3 x 10.2
Package Shipping Weight (kg)	7.6
Package Shipping Weight (lbs)	16.76

Humidity
70% non-condensing

Interoperability
Use up to two units with NV-SUBAMP200-xx

Mounting

In-Wall Square Cutout	310mm x 310mm (12" x 12")

High Level Input Connector
Gold Plated Spring Loaded Binding Posts

Speaker Size
8" (200mm) High-Output

Enclosure Type
Sealed

Sensitivity
85dB

Frequency
35-200Hz

Speaker Impedance
8 Ohm

Power Consumption
125W RMS
250W Peak

Regulatory Approvals
RoHS (Restriction of Hazardous Substances Directive 2002/95/EC

Legrand reserves the right to change specifications without notice.

designed to be better™

legrand® | AV

Legrand, North America

3015 Kustom Drive
Hebron, KY 41048
United States
844.334.8044
www.legrand.us/nuvo