



Perfect for pantries, garages or anywhere you want lights to turn on automatically when you enter a room, and turn off again when you leave. The Auto-On/Auto-Off SensaSwitch® provides convenient lighting control by responding to your presence through motion-sensing technology. Use this motion sensor light switch on its own to control a light or fixture from a single location, or pair with additional switches to control a single light source from multiple locations (3 or 4-way applications).

This switch\* features enduring Microban® antimicrobial technology that works to reduce the growth of bacteria, around the clock, for the lifespan of the product.

\* Existing inventory of switches, dimmers and plastic wall plates from the adorne® Collection at some partner locations may not yet include Microban® protection. To confirm that a specific Legrand product is protected with Microban®, check that the exterior of the product packaging includes a green dot or a "Protected with Microban" label.

Made exclusively for use with screwless Wall Plates from the adorne® Collection, sold separately.

No antimicrobial efficacy claims are being made or are valid with respect to products sold in Canada.

## Features & Benefits

Helps fight the growth of stain and odor-causing bacteria through the invisible and continuous product protection of Microban® antimicrobial technology

Installs in 15 minutes or less, fitting into an existing electrical box. No new wiring required for typical installation.

Usable in single-pole or 3-way applications. Must be paired with another SensaSwitch or SensaDimmer for 3-way control.

For complete installation, device must be paired with an adorne® screwless Wall Plate (not included). Available in a range of contemporary colors and stunning finishes.

Features motion-sensing technology for automatic on/off lighting control. (Auto shut-off can be set from 5 to 30 minutes after vacancy.)

More color options available to fit any style, including finishes to match current hardware and lighting trends.

## Specifications

### General Info

Product Line	Pass & Seymour	Replaced by Part Number	
Color	Magnesium	Country Of Origin	China
Features	Antimicrobial Protection, Motion Sensor	Switch Type	Motion Sensor
Number of Switches	1	Standard	cULus

---

Warranty Type	Limited Lifetime Warranty
---------------	---------------------------

---

## Dimensions

---

Product Width US	1.85 in	Product Depth US	1.77 in
------------------	---------	------------------	---------

---

Product Height US	2.66 in
-------------------	---------

---

## Technical Information

---

Connector	Screw Terminals	Sensor Type	Occupancy, Vacancy
-----------	-----------------	-------------	--------------------

---

Number of Gangs	1	Number of Poles	4-Way, Single Pole
-----------------	---	-----------------	--------------------

---

Mounting Type	Box	Sensing Range	600 sq ft, 180 degrees
---------------	-----	---------------	------------------------

---

Connection Type	Internal Pressure Plates	Sensitivity	Major Motion 35', Minor Motion 20'
-----------------	--------------------------	-------------	---------------------------------------

---

Load	Incandescent or LED lamp: 0-600 Watt Fluorescent lamp: 0-600 VA Fan Motor: 1/6 hp	Environmental Conditions	Residential Indoor Use Only
------	--	--------------------------	-----------------------------

---