



From bedrooms to basements, this motion sensor switch is perfect for anywhere you might want to worry (or waste electricity) less. A conveniently modern light switch, it features combination control that allows you to manually turn lights on when entering a room, and then automatically turns the lights off for you when you leave. Use this device on its own to control a light or fixture from a single location one location, or combine with additional switches for controlling a single light source from multiple locations in 3 or 4-way applications.

This switch* features enduring Microban® antimicrobial technology that works to reduce the growth of bacteria, around the clock, for the lifespan of the product.

* Existing inventory of switches, dimmers and plastic wall plates from the adore® Collection at some partner locations may not yet include Microban® protection. To confirm that a specific Legrand product is protected with Microban®, check that the exterior of the product packaging includes a green dot or a "Protected with Microban" label.

Made exclusively for use with screwless Wall Plates from the adore® Collection, sold separately.

No antimicrobial efficacy claims are being made or are valid with respect to products sold in Canada.

Features & Benefits

Helps fight the growth of stain and odor-causing bacteria through the invisible and continuous product protection of Microban® antimicrobial technology

Installs in 15 minutes or less, fitting into an existing electrical box. No new wiring required for typical installation.

Usable in single-pole or 3-way applications. Must be paired with another SensaSwitch or SensaDimmer for 3-way control.

For complete installation, device must be paired with an adore® screwless Wall Plate (not included). Available in a range of contemporary colors and stunning finishes.

Uses SensaSwitch technology to automatically turn lights off after you leave. (Auto shut-off can be set from 5 to 30 minutes after vacancy.)

More color options available to fit any style, including finishes to match current hardware and lighting trends.

Specifications

General Info

Product Line	Pass & Seymour	Color	White
Country Of Origin	China	Features	Antimicrobial Protection, Motion Sensor
Switch Type	Motion Sensor	Number of Switches	1

Standard	cULus	Warranty Type	Limited Lifetime Warranty
Dimensions			
Product Width US	1.77 in	Product Depth US	1.85 in
Product Height US	2.66 in		
Technical Information			
Connector	Screw Terminals	Sensor Type	Vacancy
Number of Gangs	1	Number of Poles	3-Way, Single Pole
Mounting Type	Box	Sensing Range	600 sq ft, 180 degrees
Connection Type	Internal Pressure Plates	Sensitivity	Major Motion 35', Minor Motion 20'
Load	Incandescent or LED lamp: 0-600 Watt Fluorescent lamp: 0-600 VA Fan Motor: 1/6 hp	Environmental Conditions	Residential Indoor Use Only