

## Wiremold Charging Station, 2-Gang, (2) Duplex GFCI - Bronze Part No. XCSPP2GRR-BZ



The Power Pedestal is ideal for areas that are already illuminated, such as outdoor dining areas. Shorter height enables use besides tables or as a lower-profile solution in landscaping. Station includes two duplex GFCI receptacles.

## Features & Benefits

Charging & Illumination - Combine power with area lighting in one pedestal to maximize functionality of outdoor spaces.

Outdoor-Rated Construction – Rugged aluminum form designed for durability in all weather conditions. UL listed to NEMA 3R requirements to ensure optimal performance.

in three outdoor-rated finishes to complement your space design. Choose from black, bronze or silver.

Durable, Premium Finishes - Available A/V & Communication Compatible - Add an A/V-Communication Kit to 3-gang versions to accommodate Wiremold AVIP plates as well as decorator A/V or communication devices. Enables pedestal to support outdoor presentation areas and classrooms, eliminating the need to bring cables from inside a building.

shelves to hold mobile devices while charging

Device Shelves - Add up to two pairs of Door Options - Interior illuminates when door is open. Replace standard colormatched door with a transparent version to make devices inside more visible. Or, select a lockable door for added security or to ensure use is limited to facility personnel.

## Specifications

| General Info          |                   |                   |   |
|-----------------------|-------------------|-------------------|---|
| Product Line          | Wiremold          | Color             | Bronze  |
| UPC Number            | 786776186307      | Country Of Origin | Mexico  |
| Number of Receptacles | 2                 | Outlet Type       | Weather-Resistant                                   |
| Application Sector    | Commercial        | Standard          | cULus Listed, File<br>Number E479489, Guide<br>PUPR |
| Туре                  | Charging Stations | Installed Devices | GFCI  |
| Dimensions            |                   |                   |   |
| Product Width US      | 6.0 in            | Product Weight US | 35.0 lb   |

| Product Height US           | 34.0 in    | Product Length US             | 8.0 in   |  |  |
|-----------------------------|------------|-------------------------------|----------|--|--|
| Listing Agencies / 3rd Part | y Agencies |                               |          |  |  |
| cULus ListingNumber         | E479489    | cULus Listed                  | Yes      |  |  |
| Buy American Act Compliance |            |                               |          |  |  |
| NAFTA                       | Yes        |                               |          |  |  |
| Additional Information      |            |                               |          |  |  |
| RoHS Conformant             | Yes        | Product Environmental Profile | Yes      |  |  |
| Technical Information       |            |                               |          |  |  |
| Is Pre-Wired                | Yes        | Number of Gangs               | 2        |  |  |
| Amperage                    | 20 A       | Lighting Types                | No Light |  |  |