


# QUICK TIPS

## ADORNE® FURNITURE POWER CENTER

+ PART NUMBERS

+ WALL PLATES



# + PART NUMBERS


## + WALL PLATES



### What do the adorne Furniture Power Center part numbers mean?

Here's a breakdown of how the part numbers are built. Generally speaking, you start with the number of gangs, move into the unit types, then finish with the color options.

#### Example:



### How do I know the number of units I need?

It depends on the number of gangs. For example, a 1-gang solution will need one unit, a 2-gang solution will need two units, etc. Keep in mind that if you choose either the Half Paddle Switch or Half USB Charging Port, you'll need another half unit to create a 1-gang solution.

### How many switches and outlets can I have per unit?

With the adorne Furniture Power Center, you are limited to two switches or four outlets per unit.

### What is a mirrored pair?

A mirrored pair is a right and left version of the same adorne Furniture Power Center. It is used primarily in king rooms on either side of the headboard.

### What does hardwired mean?

A hardwired adorne Furniture Power Center will not come with a plug-in receptacle. It will have an MC cable with a whip.

### Which ones are standard product?

The following options are only stocked in small quantities for mock rooms. They are MTO for production.

PART NUMBER	DESCRIPTION
AD1-RU-M	Furniture Power, Outlet, and USB port, Magnesium
AD1-RU-W	Furniture Power, Outlet, and USB port, White
AD2-2UR-M	Furniture Power, 2 Gang Outlet, and 2 USB ports, Magnesium
AD2-2UR-W	Furniture Power, 2 Gang Outlet, and 2 USB ports, White
AD2-PUR-M	Furniture Power, 2 Gang Outlet, 1 USB port, 1 Half Paddle Switch Magnesium
AD2-PUR-W	Furniture Power, 2 Gang Outlet, and 1 USB port, 1 Half Paddle Switch, White
AD3-R2UR-M	Furniture Power, 3 Gang, 2 Outlets with 2 USB ports, Magnesium
AD3-R2UR-W	Furniture Power, 3 Gang, 2 Outlets with 2 USB ports, White
AD3-2UPDR-M	Furniture Power, 3 Gang, Duplex Receptacle, 2 USB Ports, 1 Paddle Dimmer, Magnesium
AD3-2UPDR-W	Furniture Power, 3 Gang, Duplex Receptacle, 2 USB Ports, 1 Paddle Dimmer, White
AD3-2UPPR-M	Furniture Power, 3 Gang, Duplex Receptacle, 2 USB Ports, 2 Half Paddle Switches, Magnesium
AD3-2UPPR-W	Furniture Power, 3 Gang, Duplex Receptacle, 2 USB Ports, 2 Half Paddle Switches, White

The following options are an example of some of the custom configurations. You are not limited to these for custom configurations.

PART NUMBER	DESCRIPTION
AD1-R-M	Furniture Power 1-GANG 1 Outlet, Magnesium
AD1-R-W	Furniture Power 1-GANG 1 Outlet, White
AD3-2UPSR-M	Furniture Power 3-GANG 2USB,Paddle Switch ,1 Outlet ,Magnesium
AD3-2UPSR-W	Furniture Power 3-GANG 2USB,Paddle Switch ,1 Outlet ,White
AD3-2UTDR-M	Furniture Power 3-GANG 2USB, softTap Dimmer,1 Outlet ,Magnesium
AD3-2UTDR-W	Furniture Power 3-GANG 2USB, softTap Dimmer,1 Outlet ,White
AD3-2UHR-M	Furniture Power 3-GANG 2USB, Whisper Switch,1 Outlet ,Magnesium
AD3-2UHR-W	Furniture Power 3-GANG 2USB, Whisper Switch,1 Outlet ,White
AD3P-R2UPP-M	Furniture Power 3-GANG 2 half Paddle Switches,2USB,1 Outlet 3 way switching, comes in a pair (2 FPCs),Magnesium
AD3P-R2UPP-W	Furniture Power 3-GANG 2 half Paddle Switches,2USB,1 Outlet 3 way switching, comes in a pair (2 FPCs),White

+ PART NUMBERS

# + WALL PLATES



## How do I purchase wall plates?

A limited selection of 1-gang, 2-gang and 3-gang colors are available through Wiremold. All wall plates purchased through Wiremold are sold in packs of 10. When purchasing wall plates for mirrored pair you would need to purchase two wall plates per pair. For example, one unit will require two wall plates, two units will require four wall plates, etc.

The following wall plate options are available to order through Wiremold.

CATALOG NUMBER	DESCRIPTION
AD1WP	1-Gang Furniture Power Center Wall Plate
AD2WP	2-Gang Furniture Power Center Wall Plate
AD3WP	3-Gang Furniture Power Center Wall Plate

### COLOR OPTIONS

Add color references listed below to part number



- AT - Ashen Tan
- BR - Painted Bronze
- BS - Brushed Stainless Steel
- CP - Cappuccino
- GG - Greige
- GR - Painted Graphite
- LA - Light Almond
- MB - Mirror Black
- MG - Magnesium
- MO - Moss Gray
- MS - Brushed Stainless
- MW - Mirror White
- NK - Black Ink
- OB - Oil-Rubbed Bronze
- PW - Powder White
- SN - Satin Nickel
- TF - Truffle
- TM - Painted Titanium
- WH - Glossed White
- WHW - White on White