





Fiber Trough Cross Reference

DESCRIPTION >	STRAIGHT SECTION	FITTINGS		
ITEM NUMBER >	FT	FTFB90	FTFB45	FTVI90
				
TRAY DIMENSIONS (HxW)				
2" x 2" / 50 x 50 mm	FT 50/50	FTFB90 50/50	FTFB45 50/50	FTVI90 50/50
2" x 4" / 50 x 100 mm	FT 50/100	FTFB90 50/100	FTFB45 50/100	FTVI90 50/100
2" x 8" / 50 x 200 mm	FT 50/200	FTFB90 50/200	FTFB45 50/200	FTVI90 50/200
2" x 12" / 50 x 300 mm	FT 50/300	FTFB90 50/300	FTFB45 50/300	FTVI90 50/300
4" x 4" / 100 x 100 mm	FT 100/100	FTFB90 100/100	FTFB45 100/100	FTVI90 100/100
4" x 8" / 100 x 200 mm	FT 100/200	FTFB90 100/200	FTFB45 100/200	FTVI90 100/200
4" x 12" / 100 x 300 mm	FT 100/300	FTFB90 100/300	FTFB45 100/300	FTVI90 100/300
4" x 20" / 100 x 500 mm	FT 100/500	FTFB90 100/500	FTFB45 100/500	FTVI90 100/500
4" x 24" / 100 x 600 mm	FT 100/600	FTFB90 100/600	FTFB45 100/600	FTVI90 100/600
CORRESPONDING COVER	FTC	FTCFB90	FTCFB45	FTCVI90

DESCRIPTION >	FITTINGS				
ITEM NUMBER >	FTV090	FTT	FTB	FTX	FTVT
					
TRAY DIMENSIONS (HxW)					
2" x 2" / 50 x 50 mm	FTV090 50/50	FTT 50/50	FTB 50/50	FTX 50/50	FTVT 50/50
2" x 4" / 50 x 100 mm	FTV090 50/100	FTT 50/100	FTB 50/100	FTX 50/100	FTVT 50/100
2" x 8" / 50 x 200 mm	FTV090 50/200	FTT 50/200	FTB 50/200	FTX 50/200	FTVT 50/200
2" x 12" / 50 x 300 mm	FTV090 50/300	FTT 50/300	FTB 50/300	FTX 50/300	FTVT 50/300
4" x 4" / 100 x 100 mm	FTV090 100/100	FTT 100/100	FTB 100/100	FTX 100/100	FTVT 100/100
4" x 8" / 100 x 200 mm	FTV090 100/200	FTT 100/200	FTB 100/200	FTX 100/200	FTVT 100/200
4" x 12" / 100 x 300 mm	FTV090 100/300	FTT 100/300	FTB 100/300	FTX 100/300	FTVT 100/300
4" x 20" / 100 x 500 mm	FTV090 100/500	FTT 100/500	FTB 100/500	FTX 100/500	FTVT 100/500
4" x 24" / 100 x 600 mm	FTV090 100/600	FTT 100/600	FTB 100/600	FTX 100/600	—
CORRESPONDING COVER	FTCV090	FTTC	FTBC	FTXC	included