

# DATA SHEET



## 2-Port HDMI® Splitter 4K30

Split a single HDMI audio/video signal from a source device to two monitors or projectors

### OVERVIEW

The 2-Port HDMI Splitter 4K30 is a 1-Input 2-Output splitter supporting up to 4k30 video, ideal for applications requiring the HDMI 1.4 standard. A perfect solution for connecting a computer, Blu-ray™ player, gaming console, media server, or A/V receiver to two HDMI monitors or projectors.

The HDMI splitter is HDCP 1.4 compliant and supports exceptional 4K UltraHD resolutions up to 3840 x 2160 at 30hz, handling total HDMI data rates up to 10.2Gbps.

### FEATURES

- One HDMI input and two HDMI outputs
- Supports resolutions up to 3840 x 2160 at 30hz
- HDCP 1.4 Compliant
- Supports 340MHz/3.4Gbps per channel
- Supports 3D formats
- Supports 8, 10 & 12bit per channel deep color
- Supports DTS-HD, Dolby TrueHD, DTS, Dolby AC3 & DSD Audio

### ITEM DESCRIPTION

41057

2-Port HDMI® Splitter 4K30

designed to be better.™



# DATA SHEET

## SPECIFICATIONS: 2-Port HDMI® Splitter 4K30

### ELECTRICAL SPECIFICATIONS:

- Electrical Input: 100-240V 50/60HZ, 0.3A max
- Electrical Output: 5V DC@1A
- Power Adapter Plug: US/UK/EU Type

### PHYSICAL SPECIFICATIONS:


- Operating Temperature: -15°C to +55°C
- Storage Temperature: -25°C to +70°C
- Operating Humidity: 5% to 90 % RH (no condensation)

### SIGNAL SPECIFICATIONS:

- Output Video: HDMI
- HDMI Input/output Connector: Type A 19 pin
- Panel Refresh Rate: 30Hz
- Video Amplifier Bandwidth: 3.4Gbps/340MHz (10.2Gbps)
- Supported Resolutions: 480p,576p,1080i,1080p 3840x2160/30hz

### PHYSICAL CHARACTERISTICS:

- Dimensions (HxWxL): 23mmH x 55mmW x 105mmL  
(0.86 inch H x 2.16 inch W x 4.13 inch L)
- Weight(Net): 80g (.18lb)
- Approvals: CE Marked and Conforms to 2011/65/EU ROHS2



Legrand, North and Central America

60 Woodlawn Street  
West Hartford, CT 06110  
1.877.BY.LEGRAND (295.3472)  
www.legrand.us