


Nuvo® P30 Touch Screen

Easy-to-access control—when you need it.

The Nuvo P30 Touch Screen (NV-P30-XX) is a seven inch Android tablet that offers convenient, complete, in-wall control of the Player Portfolio System. The P30 runs the Player Portfolio app and Spotify for seamless and unified control of your home audio; allowing access to your favorite streaming services or music stored on networked devices.



9/16" (14.3mm)
depth when mounted



- Convenient, complete, in-wall control of the Nuvo Player Portfolio system
- Runs the Player Portfolio app and Spotify for seamless control of your home audio, including streaming services and music stored on networked devices
- Wall-mounted tablet allows access to other apps, like Spotify, Pandora, and more
- Sleek, high contrast seven inch 1024 x 600 IPS capacitive touch screen
- Connects simply with a single RJ45 802.11af PoE cable
- Universal mounting plate

*Streaming services subject to geographic availability. Service subscriptions may be required.



Nuvo® P30 Touch Screen

Physical Specifications

Material	Plastic
Color	BK-Black or WH-White
Unit Size (mm)	130.17 H x 196.85 W x 25.4 D
Unit Size (in)	5.125 H x 7.75 W x 1 D
Shipping Unit Size (mm)	148 H x 217 W x 63.25 D
Shipping Unit Size (in)	5.82 H x 8.54 W x 2.49 D
Unit Weight (kg)	0.453
Unit Weight (lbs)	1
Shipping Unit Weight (kg)	0.512
Shipping Unit Weight (lbs)	1.13
Connections and Capabilities	
Local Area Network (LAN)	(RJ45, Cat5 minimum, 10/100baseT minimum, POE 802.3AF Class 1 compatible)
Network Connectivity	Ethernet
Power Supply	Internal

SPECIFICATIONS

Power Consumption (max)	802.3af Class 1
Power Consumption (typical)	802.3af Class 1
Operating Temperature (celsius)	0 - 40 degrees
Operating Temperature (fahrenheit)	32 - 104 degrees
Humidity	70% Non-Condensing
Regulatory Approvals - Safety	Not Required
Regulatory Approvals - EMC	US:FCC CFR Title 47 Part 15, Subpart B; CANADA:ICES-003; EUROPE:CISPR13; EUROPE: 55020; AUSTRALIA/NEW ZEALAND: C-TICK standard AS/NZS CISPR13
Regulatory Approvals - Environmental	RoHS (Restriction of Hazardous Substances Directive 2002/95/EC)
Languages Supported	English, Spanish, French Portugese, German, Italian

Legrand reserves the right to change specifications without notice.

designed to be better™



Legrand, North America

3015 Kustom Drive
Hebron, KY 41048
United States
844.334.8044
www.legrand.us/nuvo