

NUVO

P20 PoE Keypad

The Nuvo Arteor PoE Keypad (NV-P20-ARXX), Nuvo Livinglight PoE Keypad (NV-P20-LLXX), and Nuvo Valena PoE Keypad (NV-P20-VLXX) offer convenient in-wall control of core functions of a single zone of any Player Portfolio system. The P20 offers users easy command of volume, play, and pause, as well as next/previous track navigation, and additional access to five system preset favorites.



NV-P20-ARWH

* Wall plates sold separately



With its sleek backlit design and available color options, the P20 pairs simplicity with style. The P20 works in harmony with the Nuvo Player app to keep both control methods in perfect sync, and is powered by a single RJ45 PoE connection.

- Convenient in-wall control of play, pause, volume, and track navigation
- A single button to access 5 system preset favorites
- White capacitive touch backlit display
- Single wire connectivity via 802.3af PoE
- Setup is easy via Player app, no PCs required
- NV-P20-ARXX part numbers are designed to fit the Arteor line of wall plates
- NV-P20-LLXX part numbers are designed to fit the Livinglight line of wall plates
- NV-P20-VLXX part numbers are designed to fit the Valena line of wall plates

Nuvo P20 PoE Keypad

SPECIFICATIONS

Arteor



The image shows the Nuvo P20 Arteor Keypad, a white plastic device with a square face. It features a central play/pause button (II), a stop button (X), and a power button (I). Below these are five numbered buttons (1-5) and a music note icon. The keypad is shown from a front-facing perspective.

NV-P20-ARWH
Nuvo P20 Arteor Keypad
White

Livinglight



The image shows the Nuvo P20 Livinglight Keypad, a white plastic device with a square face. It features a central play/pause button (II), a stop button (X), and a power button (I). Below these are five numbered buttons (1-5) and a music note icon. The keypad is shown from a front-facing perspective.

NV-P20-LLN
Nuvo P20 Livinglight Keypad
White

Valena



The image shows the Nuvo P20 Valena Keypad, a white plastic device with a square face. It features a central play/pause button (II), a stop button (X), and a power button (I). Below these are five numbered buttons (1-5) and a music note icon. The keypad is shown from a front-facing perspective.

NV-P20-VLAL
Nuvo P20 Valena Keypad
Aluminum

Physical Specifications:	
Material:	Plastic
Color:	White, Magnesium — Arteor White, Anthracite, Light Tech — Livinglight White, Ivory, Aluminum — Valena
Unit Size (mm):	45 x 45
Unit Size (in):	1.77 x 1.77
Shipping Unit Size (mm):	133.35 x 66.675 x 133.35
Shipping Unit Size (in):	5.25 x 2.625 x 5.25
Unit Weight (kg):	0.063503
Unit Weight (lbs):	0.14
Shipping Unit Weight (kg):	0.199581
Shipping Unit Weight (lbs):	0.44

Technical Specifications:	
Local Area Network (LAN):	(RJ45, Cat5 minmum, 10/100baseT minimum, PoE 802.3af Class 1 compatible)
Network Connectivity:	Ethernet
Power Supply:	802.3af Class 1 compatible
Power Consumption (max):	802.3af Class 1
Power Consumption (typical):	802.3af Class 1
Operating Temperature (celsius):	0 - 40 degrees
Operating Temperature (fahrenheit):	32 - 104 degrees
Humidity:	70% Non-Condensing
Regulatory Approvals - EMC:	US:FCC CFR Title 47 Part 15, Subpart B; CANADA:ICES-003; EUROPE:CISPR13; EUROPE: 55020; AUSTRALIA/NEW ZEALAND: C-TICK standard AS/NZS CISPR13
Regulatory Approvals - Environmental:	RoHS (Restriction of Hazardous Substances Directive 2002/95/EC)

Legrand reserves the right to change specifications without notice.

NUVO

LEGRAND | AV RESIDENTIAL BRANDS
Chief | Da-Lite | Luxul | Middle Atlantic | Nuvo | On-Q | SANUS