





SLOTTED OPENINGS ARE
OFFSET STAGGERED
FROM SIDE TO SIDE



NOTES:

- ALL SIZES AVAILABLE IN 6.3 FT (2 METER) LENGTHS.
- TWO PLACE DECIMAL DIMENSIONS ARE APPROX. DUE TO METRIC TO INCH CONVERSION.
- FIRE RETARDENT PLASTIC, HALOGEN FREE, UL-94VO RATED.
- IT IS RECOMMENDED TO SUPPORT THE RACEWAY EVERY 36" (900mm).
- MOUNTING BRACKETS SHOULD BE MOUNTED CLOSE TO A JOINER IF POSSIBLE.

SIZE IN/(MM)	ORTRONICS P/N	COLOR
2" X 2" (50 X 50)	MMFSLC2X2-Y	YELLOW
4" X 2" (100 X 50)	MMFSLC4X2-Y	YELLOW
4" X 4" (100 X 100)	MMFSLC4X4-Y	YELLOW
4" X 8" (100 X 220)	N/A	N/A
12" X 4" (100 X 300)	N/A	N/A

NOTE: REPLACE "Y" FOR YELLOW WITH "B" FOR BLACK OR "O" FOR ORANGE. MINIMUM QUANTITIES REQUIRED. CONTACT YOUR CUSTOMER SERVICE REPRESENTATIVE (CSR)

*** NOTICE ***
THIS DOCUMENT CONTAINS CONFIDENTIAL AND/OR PROPRIETARY INFORMATION INTENDED FOR USE ONLY BY THE INDIVIDUAL(S) PROVIDED. NEITHER THIS DOCUMENT, NOR ANY INFORMATION CONTAINED HEREIN, MAY BE COPIED, DISTRIBUTED, DISCLOSED TO ANY THIRD PARTY OR USED IN ANY MANNER OTHER THAN FOR WHICH IT HAS BEEN PROVIDED, WITHOUT THE PRIOR WRITTEN CONSENT OF ORTRONICS, INC. MANUFACTURING RELEASE, PRODUCT SPECIFICATIONS AND STANDARDS ARE SUBJECT TO CHANGE WITHOUT NOTICE.



125 EUGENE O'NEILL DRIVE
NEW LONDON, CT 06320
TEL: 860-445-3800
FAX: 860-405-2990
WWW.ORTRONICS.COM

TITLE

MM FIBER RACEWAY, SLOTTED DUCT
WITH COVER

	NAME	DATE	SIZE	CAD FILE	DWG NO	REV
DWN	J.QUINN	03/27/12	A	MMFSLCXXxYYZC	OR-MMFSLCXXxYY-Z	00
CHK	J.LUCY	05/01/12	SCALE	1:48	WEIGHT	SHEET
APPR	C.VACCA	05/01/12				1 OF 1