

Protect electrical connections from liquids, contaminants, and corrosive elements.

LTB-SS Series

Rated IP68 and NEMA 4X, Stainless Steel Liquid-Tight Connectors offer corrosion resistance for the toughest environments. For use in wet or dry locations to seal electrical connections against dust, dirt, oil, water, chemicals and other corrosive elements. These are available in straight and 90 degree, 3/8" to 2" NPT. The stainless steel liquid-tight offering includes a nylon-insulated throat and Viton® O-Ring.



Features & Benefits



- **304 grade stainless steel construction** resists corrosion and impacts
- **Includes a nylon-insulated throat and embedded Viton® O-Ring** to ensure a watertight seal
- **Rated IP68 and NEMA 4X for use in wet or dry locations** to seal electrical connections against dust, dirt, oil, water, chemicals and other corrosive elements
- **Available in** straight and 90 degree, 3/8" to 2"
- **Stainless Steel Liquid-Tight Connectors** are ideally suited for OEM and MRO applications known for their corrosive and abusive environments

3rd Party Compliance



Most Flexcor products have UL and/or CSA approvals. Please consult factory for approval information. Conforms to NEMA 3R.

Ordering Information

Stainless Steel Liquid-Tight Fittings

Straight Male Catalog Number	90° Male Catalog Number	NPT Size
LTB50SS	LTB5090SS	1/2"
LTB75SS	LTB7590SS	3/4"
LTB100SS	LTB10090SS	1"
LTB125SS	LTB12590SS	1 1/4"
LTB150SS	LTB15090SS	1 1/2"
LTB200SS	LTB20090SS	2"

Country of Origin: Turkey



**Stainless Steel Straight
Liquid-Tight Fitting**



**Stainless Steel
90° Liquid-Tight Fitting**

Most Flexcor products have UL and/or CSA Approvals.
Please contact factory for approval information.

Field Uses/Vertical Markets

- Temporary Power
- Industrial Manufacturing
- Maintenance Repair Operations
- Panel Building
- Utilities
- Renewable Energy

Also available...

- Hospital Grade Devices
- PlugTail® Devices
- SPD & Isolated Ground Devices
- Ground Continuity Monitoring (GCM)
- Straight Blade Plugs & Connectors
- Turnlok® Locking Devices
- Weatherproof Boxes & Covers
- IEC 309 Industrial Products
- Portable GFCIs

 The paper used to print this document is an environmentally responsible paper with 10% post consumer waste, with FSC and SFI Chain of Custody certifications, Lacey Act compliant. 100% of the electricity used to manufacture Flo sheets is generated with Green-e certified renewable energy.

All brand and product names referenced in this document are registered trademarks or trademarks of their respective holders.



Legrand, North America
60 Woodlawn Street
West Hartford, CT 06110
1.877.BY.LEGRAND (295.3472)
www.legrand.us

570 Applewood Crescent
Vaughan, Ontario L4K 4B4
905.738.9195
www.legrand.ca

FOLLOW US

