



TSD703PTC

Energy-saving dimming for Incandescent loads.

TSD703P*/TSD1103P*

Replace your standard switch with the new Toggle Slide Dimmer by Legrand. The ergonomic slider was designed with the end user in mind, making it easier to adjust in the dark or on the run.

Compatible with incandescent dimmable bulbs, these dimmers feature constant memory that returns lights to the previous level after a power failure for automatic control and convenience.


*Denotes color suffix

Features & Benefits

New aesthetically pleasing ergonomic design allows for easier operation

Constant memory returns lights to previous levels after a power failure

Screw-pressure-plate backwire terminals save time, space and money




TSD703PW

Interchangeable face plates available in seven colors (TSDKIT*; sold separately)

Convenient operation – combines ON/OFF toggle switch with separate slider for dimming control

- Preset, Single Pole and 3-Way operation.
- Lifetime warranty.

3rd Party Compliance

 cULus listed, UL1472, CSA

Technical Information**Performance****Electrical**


Supply Voltage	120VAC
Ratings	700W; 1100W Incandescent
Frequency	60Hz
Installation	Single Pole or 3-Way

Environmental

Application	Indoor Use Only
-------------	-----------------

Mechanical

Enclosure Material	Polycarbonate
--------------------	---------------

**TSD1103PW****Warranty**

Lifetime

Ordering Information

Incandescent Dimmers


Catalog Number	Description	Color	Voltage	Rating
TSD703PTC	Preset, Single Pole and 3-Way	Three interchangeable Face Colors: Ivory, White, Light Almond	120VAC 60Hz	700W Inc
TSD703PW	Preset, Single Pole and 3-Way	Face Color: White	120VAC 60Hz	700W Inc
TSD703PLA	Preset, Single Pole and 3-Way	Face Color: Light Almond	120VAC 60Hz	700W Inc
TSD703PI	Preset, Single Pole and 3-Way	Face Color: Ivory	120VAC 60Hz	700W Inc
TSD703P	Preset, Single Pole and 3-Way	Face Color: Brown	120VAC 60Hz	700W Inc
TSD703PBK	Preset, Single Pole and 3-Way	Face Color: Black	120VAC 60Hz	700W Inc
TSD703PRED	Preset, Single Pole and 3-Way	Face Color: Red	120VAC 60Hz	700W Inc
TSD703PGRY	Preset, Single Pole and 3-Way	Face Color: Gray	120VAC 60Hz	700W Inc
TSD1103PTC	Preset, Single Pole and 3-Way	Three interchangeable Face Colors: Ivory, White, Light Almond	120VAC 60Hz	1100W Inc
TSD1103PW	Preset, Single Pole and 3-Way	Face Color: White	120VAC 60Hz	1100W Inc
TSD1103PLA	Preset, Single Pole and 3-Way	Face Color: Light Almond	120VAC 60Hz	1100W Inc
TSD1103PI	Preset, Single Pole and 3-Way	Face Color: Ivory	120VAC 60Hz	1100W Inc
TSD1103P	Preset, Single Pole and 3-Way	Face Color: Brown	120VAC 60Hz	1100W Inc
TSD1103PBK	Preset, Single Pole and 3-Way	Face Color: Black	120VAC 60Hz	1100W Inc
TSD1103PRED	Preset, Single Pole and 3-Way	Face Color: Red	120VAC 60Hz	1100W Inc
TSD1103PGRY	Preset, Single Pole and 3-Way	Face Color: Gray	120VAC 60Hz	1100W Inc
TSDKIT		Brown		
TSDKITBK		Black		
TSDKITGRY		Gray		
TSDKITI	Interchangeable Faces	Ivory		
TSDKITLA		Light Almond		
TSDKITW		White		
TSDKITRED		Red		

Vertical Markets

- Office
- Residential
- Multiple Dwelling
- Hospitality/Lodging

Available in the radiant® collection

- GFCI Receptacles
- Tamper-Resistant and Standard Duplex Receptacles
- Paddle Switches
- Fan Controls
- Sensors
- Timers
- Home Automation Controls
- USB Charging Devices
- Night Lights
- Screwless Wall Plates

 The paper used to print this document is an environmentally responsible paper with 10% post consumer waste, with FSC and SFI Chain of Custody certifications, Lacey Act compliant. 100% of the electricity used to manufacture Flo sheets is generated with Green-e certified renewable energy.

All brand and product names referenced in this document are registered trademarks or trademarks of their respective holders.



Legrand, North America
60 Woodlawn Street
West Hartford, CT 06110
1.877.BY.LEGRAND (295.3472)
www.legrand.us
905.738.9195
www.legrand.ca

