



**Quad USB Chargers designed with safety and reliability in mind.**

TM8USB4\*CC6

The new radiant® Quad USB Chargers are designed to charge four mobile devices simultaneously. These devices are intended for the residential and hospitality markets and boast a slim 1.3" design to fit easily into any standard electrical box and, as part of the radiant® collection, now offer a better form and finish. This product features an overall 4.2A USB charging capability and screw-pressure-plate back wiring makes installation fast and easy.

**Features & Benefits**

**Overall 4.2A total charging capability –**  
 Four 5-volt DC USB ports that work with USB 2.0 & 3.0 compatible devices.

**Slim 1.3" depth fits easily into any box.**

**Accepts standard wallplates.**



TM8USB4LACC6

**Multiple color options available.**


**Back and side wire terminals accommodate #14 AWG - #10 AWG stranded and solid wire.**

**Zinc-plated ground terminal screw.**

- Part of the radiant® collection.
- Charge multiple USB powered devices at the same time.
- Allow users to plug USB cables directly without AC adapters or transformer style plugs.

- Compatible with USB 2.0 and 3.0 devices.
- Accepts standard Pass & Seymour wall plates and radiant® screwless wall plates.
- Compact design.

**Compliance**

 cULus Listed. Complies with test requirements UL1310.

## Technical Information

### Performance

#### Electrical

Dielectric Withstand Voltage	Withstands 1500V minimum
Maximum Working Voltage	125VAC input, 5VDC, 4.2A output
No Load Power	.04 Watts

#### Mechanical


Terminal Identification	Terminal Identification in accordance with UL498 (Brass, White, Green)
Terminal Accommodation	#14 AWG – #10 AWG copper conductor only
Product Identification	Ratings are permanent part of the device

#### Environmental

Flammability	UL94 V2 (for device cover) 5V (for device body and frame)
Operating Temperature	Maximum continuous +60°C, minimum -40°C

### Materials

Face	Polycarbonate
Body	Polycarbonate
Contacts	CDA 260 Brass
Mounting Strap	.049" Zinc-Plated Steel
Terminal Screws	Tri-Drive Zinc Plated Steel with Either Clear or Yellow Chromate for color identification
Ground Screw	Tri-Drive Steel with Green Chromate
Mounting Screws	Tri-Drive Steel




### Warranty

1 Year

---

## Ordering Information

### radiant® Quad USB Chargers

Catalog Number	Color	Total Charging Capacity	3rd Party Compliance
			 UL1310
TM8USB4BKCC6	Black	4.2 Amp	•
TM8USB4ICC6	Ivory	4.2 Amp	•
TM8USB4LACC6	Light Almond	4.2 Amp	•
TM8USB4NICC6	Nickel	4.2 Amp	•
TM8USB4WCC6	White	4.2 Amp	•

---

## Vertical Markets


- Residential
- Multi-Dwelling
- Hospitality

---

## Also available in the radiant® collection...

- Duplex USB Chargers
- GFCI Receptacles
- Paddle Switches
- Lighting Controls
- Fan Speed Controls
- Combination Devices
- Night Lights
- Screwless Wall Plates
- Timers
- Home Automation Controls
- Standard & Tamper-Resistant Receptacles

---

 The paper used to print this document is an environmentally responsible paper with 10% post consumer waste, with FSC and SFI Chain of Custody certifications, Lacey Act compliant. 100% of the electricity used to manufacture Flo sheets is generated with Green-e certified renewable energy.

All brand and product names referenced in this document are registered trademarks or trademarks of their respective holders.



**Legrand, North America**  
60 Woodlawn Street  
West Hartford, CT 06110  
1.877.BY.LEGRAND (295.3472)  
[www.legrand.us](http://www.legrand.us)

570 Applewood Crescent  
Vaughan, Ontario L4K 4B4  
905.738.9195  
[www.legrand.ca](http://www.legrand.ca)

FOLLOW US

