
RACK PDU, NETWORK METERED, ZERO U, 16A, 120V, (24) 5-20R, L5-20P CORD

LP-41200 | [Legrand](#)

FEATURES & BENEFITS

Network Metered PDUs enable line level power metering in real time. Allowing remote monitoring of the load level, custom notifications, and user specified conditions. Each Network Metered PDU provides visibility and reporting of power usage on the PDUs Color LCD screen and to tablets, smart phones, or computers from nearly anywhere.

To download the latest PDU firmware, please visit the [support page here](#).



- **Input Plug:** NEMA L5-20P
- **Output Receptacles:** (24) NEMA 5-20R, 16A
- **Networked Controller:** Enables remote and local monitoring of the PDU and peripherals
- **Load Monitoring:** View the power being drawn for the entire PDU, receive notifications of potential issues or when near max amperage draw
- **User Defined Notifications:** User defined thresholds for power draw or environmental factors with notifications if thresholds have been met
- **Remote Management:** Manage and configure the unit from any location
- **High-Resolution Color LCD:** Displays energy reading, current, and voltage; important configuration settings, alarm settings, and control outlets which simplifies commissioning
- **Integrated Locking Outlets on IEC Receptacles:** Eliminates the need for special locking cords
- **Rotatable Cord:** Enables maximum flexibility for routing the input plug—simplifying the installation of Zero U PDUs
- **Mounting Types:** Available in horizontal and vertical configurations to ensure power distribution is optimally located
- **PDU Linking:** Cascade up to 16 PDUs via Ethernet or USB—this can minimize port usage on network switches or consolidate accessibility to multiple PDUs from a single IP address
- **Hydraulic-Magnetic Breakers:** Provide less heat dependent local protection and quick recovery from circuit overload, by utilizing a two-step response curve—these breakers provide a delay on normal overcurrents, while tripping quickly on short circuits
- **Optional Environmental Sensors and Remote Locking:** Can alert of any threats of downtime or potential physical security breaches
- **Software Interoperability:** Seamlessly integrate into any monitoring software with open JSON-RPC interface
- **Software Compatibility:** SNMP, LUA, Java, JavaScript, and Perl

SPECIFICATIONS

GENERAL INFO

Color: Black / Silver
Product Series: LP-Series
Type: Power Distribution Unit

Component Type: Network Metered PDU
Input Plug Type: NEMA L5-20P

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

DIMENSIONS

Rack Units: 0

CORD INFORMATION

Cord Length Metric: 3m

TECHNICAL INFORMATION

AC Voltage Input: 120V
Amps: 16A
Mounting: Button
Capacity: 1.9kVA
Receptacle Type: 5-15R/5-20R
Number Of Receptacles: 24

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: TAIWAN