
CONTAINMENT KIT, VERT, 8'H X 15'L ALUMINUM, ROOF SUPPORTED

CFVTA815RSA | [Legrand](#)



FEATURES & BENEFITS

Contain-IT FLEX was designed to maximize efficiency while creating a predictable operating environment, ensuring maximum reliability of the equipment. The solution prevents bypass airflow and recirculation through enclosing either the hot or cold aisle of a data center.

This Vertical Containment Kit contains all the components needed to contain an aisle at the specified dimensions with a roof-supported installation using threaded rods.



- **Near Tool-less Installation:** Using components that snap together, the Contain-IT FLEX system requires only a handful of tools that can be found on any job site, allowing for easy field installs and modifications
- **Low-cost Installation:** Using a common set of components, the Contain-IT FLEX system can be adopted for any environment, eliminating the need for custom fabrication or engineering of parts
- **Faster Delivery:** Unlike other containment solutions our containment solution is reliant on a common set of components which allows them to be stocked around the country and ready for delivery to your job site
- **Unparalleled Customization:** Easily able to modify and customize the containment solution on-site and adapt to unique environmental challenges
- **Pre-built Kits:** Easily purchase the containment solution right for your application by buying premade containment kits that come with all the components needed to do a vertical or horizontal containment solution (end-of-row doors sold outside of kit)

Kit contains the following components:

- 24 x CFPMW4848 - Multiwall Panel 48" X 48"
- 6 x CFCI4 - Inside Corner, Kit Of 4
- 3 x CFCO4 - Outside Corner Kit Of 4
- 8 x CFRC12 - Panel Clip, Kit Of 12
- 3 x CFCAP4 - Cap Logo, Kit Of 4
- 3 x CFBHB8 - Hanger, Kit Of 8
- 10 x CFSB4 - Splice, Kit Of 4
- 2 x CFHWPHS - Kit Screw #12-1/2 Phillips Qty 50 W/ Bit
- 2 x CFHWTRX - Kit Screw #4-1/2 Torx Zinc Qty 100 With Bit
- 16 x CFSP348 - H Profile Panel Splice, 48"
- 21 x CFB90A - Beam, Containment, Aluminum 90"
- 6 x CFSC96 - Flap Seal, 96"
- 6 x CFB296 - Bulb Seal, 96"

SPECIFICATIONS

GENERAL INFO

Color: Black

Product Series: Contain-IT FLEX

Type: Vertical Containment Kit

Component Type: Roof Supported

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

CONSTRUCTION INFORMATION

Component 1: Kit

Material 1: Aluminum

Material 2: Aluminum

DIMENSIONS

Length (US): 15'

Width (US): 8'

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: UNITED STATES OF AMERICA

