

---

## TRULINK®; WIRELESS USB TO VGA+3.5MM AUDIO KIT

29355 | [C2G](#)

---

### FEATURES & BENEFITS

The second generation of the TruLink USB to VGA+ 3.5mm Kit provides a powerful solution to stream audio and video to a remote monitor, projector or television. Engineered to incorporate Ultra-Wide Band technology(UWB), this kit allows for in-room wireless connectivity up to 30 feet (line of sight) between the computer and display. Setup is simple and usage is seamless because all required video drivers are embedded in the host adapter. After initial software set-up, this device provides a plug and play experience for the user. Our new Quick Link feature allows additional users with host adapters to quickly connect to the device adapter with no additional steps required to “pair” the devices.

- CD-less auto-install driver installation for PC
- New QuickLink feature allows additional host adapters to connect to an existing device adapter with no pairing necessary
- WiMedia Data Rates: 53 to 480Mbps

**General Specifications**

- Data Rates (Mbps) - 53.3, 80, 106.7, 160, 200, 320, 400, 480
- Maximum Resolution - UXGA 1600x1200, WSXGA 1680x1050, 720p (1024x768, 1280x720, 1280x800) for video playback
- Operating Systems Supported - Windows XP, Vista (32 or 64bit), Windows 7 (32 or 64bit), Windows 8, Mac OSX 10.4+
- USB Standard - USB 2.0

**Wireless Specifications**

- System Standards - WiMedia PHY v1.1, Wireless USB 1.0
- WiMedia Band Groups - Band Groups 1, 3, 6 (3.1 - 8.967 GHz)
- Ultra-Wide Band Frequency - 6.3 GHz to 7.9GHz (WiMedia™ Band Group 3)
- WiMedia Channels - TFCs 1 through 10
- Range (Line of Sight) - 30ft

**Power Adapter Specifications**

- Power Input - 100-240VAC~50/60Hz, 0.5A Max
- Power Output - 5VDC, 2.5A, 12.5W Max
- Pin Diameter - 3.5mm
- Center Pin Polarity - Positive

**Physical Characteristics**

- Video Output Connector - VGA Female
- Audio Output Connector - 3.5mm Stereo Audio
- LED Light Colors - Blue=Power, Green=Link
- Housing Material - Plastic
- Operating Temperature Range - 0°-50°C
- Operating Humidity Range - 10-95%
- Weight - 0.05lbs USB Transmitter, 0.35lbs Wireless Receiver
- Dimensions - 66 x 23.1 x 12.7mm - USB Transmitter, 142.24 x 80 x 31.75mm - Wireless Receiver

---

### SPECIFICATIONS

## GENERAL INFO

Color: Silver

Product Series: TruLink

Type: Wireless VGA