



STERIGUARD™ ANTIMICROBIAL CORD DROPS

| [Pass & Seymour](#)

FEATURES & BENEFITS

SteriGuard™ Anti-Microbial Cord Drops provide excellent protection against the growth of microbes on all surfaces. Independent testing proves the ability of these devices to inhibit the growth of Escherichia coli, Gram (-) and Staphylococcus aureus, Gram (+) providing long lasting benefits to manufacturers' beyond conventional cleaning methods. Factory assembled, custom solution Cord Drops manufactured using heavy-duty SEOW/STOW cord for maximum durability and longevity meet the most demanding industrial and construction applications. SteriGuard provides a cost-effective way to add additional safety precautions and unequaled assurance that every feasible step has been taken in the interest of consumer protection. The SteriGuard™ Anti-Microbial Cord Drops with SteriGuard™ Anti-Microbial plugs and connectors are a complete anti-microbial solution.

To ensure you get the right product for your application, use the charts and follow the example below to select the right cord size and type, your required length, and the device part number. To place the order contact Customer Service at **800-223-4162** or **customer.support@legrand.us**.

PS Prefix	123 Cord Size and Type	XX Select Length	14W47AM SteriGuard Part No.
	143 = 14/3 SEOW	(1 to 99 ft.)	Select specific device from the chart.
	123 = 12/3 SEOW		Part number shown above is an example only.
	124 = 12/4 SEOW		
	103 = 10/3 SEOW		
	104 = 10/4 SEOW		
	Other sizes available upon request.		

- Patent Pending
- Custom Cord Drops are engineered to order for desired length specifications and NEMA type configurations
- Anti-microbial Additives Embedded in polymer and inhibits Growth of Bacteria, Molds, Mildews and Fungi
- Anti-microbial Additive Resistant to Scuffing and Cleaning
- Escherichia (E.Coli): - Log reduction > 4.8, reduced surface bacteria by > 99.99%
- Staphylococcus (Staph), MRSA: - Log Reduction > 4.3, reduces surface bacteria by > 99.97%
- Salmonella – Log Reduction > 3.6, reduces surface bacteria by > 99.97%
- RoHS Compliant (Non-Halogenated)

- Independently tested and Certified to JIS Z2801 standards
 - Resistant to High Pressure Hose-down applications
 - Tongue & Groove Environmental Sealing
 - Keyed Body and Cover for Alignment
 - NEMA Type 4, 4x, 6, 6P and IP67 Protection
 - Additives are embedded in both the cord and wiring devices
 - Steriguard™ Anti-microbial Cord Drops are ideal for a wide range of applications including food and beverage preparation, procession, & packaging; agriculture, pharmaceutical, and health care
-

SPECIFICATIONS

GENERAL INFO

Type: Cord

Special Features: Straight, Locking, Watertight, NEMA

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Listing Info: C22.2 No. 42M

CSA Listed: Yes

cUL Standard: Yes

UL Listing No: UL498

UL Standard: Yes

UN SPSC: 39121402

TECHNICAL INFORMATION

Amps: 15A, 20A, 30A-Wiring Devices

Material: Thermoplastic Elastomer/ Rubber

NEMA Rating: 4,4X,12,6,6P-Wiring Devices

Operating Temperature (Celsius): -40°C-60°C-Wiring Devices, -50°C- 150°C-Industrial Cord

Volts: 600V

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: UNITED STATES OF AMERICA

Buy American Act Status: Buy American Act Compliant

