



SMART TRU-UNIVERSAL DIMMER WITH HOMEKIT TECHNOLOGY

HKRL50WH | [radiant](#)

FEATURES & BENEFITS

Legrand offers a family of lighting control products for your home fully enabled to interface with Apple HomeKit. Apple HomeKit technology provides an easy, secure way to control your lights, outlets, thermostats, and more from your iPhone or iPad. With the Home app, easily and securely control all your HomeKit accessories from one location.

[Shop on Amazon.](#)



- Works with Apple HomeKit technology.
- Operates all 120V dimmable lighting types and loads.
- Use Siri, Alexa, or the Google Assistant to control your lights with just your voice.
- No hub required. Automated control and remote access requires an Apple TV with tvOS 11 or later, an iPad with iOS 11 or later, or a HomePod set up as a home hub.
- Use Legrand Home app for scenes, room grouping, automation and more.
- Easy to install with the home's existing electrical wiring (neutral required).
- Pairs with remote dimmer for multi-way control.
- Locator light for finding switch in the dark.
- Wall plate included.
- Part of the radiant® Collection.

SPECIFICATIONS

cULus Listed, UL1472, CSA-C22.2 No. 184.1-95. Conforms to NEMA WD-1 and WD-6, Supports California Title 24 Compliance, California T20 Compliant

FCC ID: YV8-SA7524

IC ID: 9922A-SA7524

EMC Regulatory Approval: Yes

SSL 7A Compliant: Yes

GENERAL INFO

Color: White
Connection Type: Certified IEEE 802.11™ b/g/n Wi-Fi® 2.4GHz radio
Style: Rocker

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes
cULus: Yes
FCC Standard: Yes
UL Listing No: UL1472
UL Standard: Yes

CONSTRUCTION INFORMATION

Material 1: Polycarbonate Lexan

DIMENSIONS

Depth (US): 1.75"
Height (US): 4.185"
Width (US): 1.787"
Weight: 0.225 lbs.

TECHNICAL INFORMATION

Compatible Power Supplies: Apple
Humidity: 0-90% relative humidity, non-condensing
Interoperability: Works with Apple HomeKit / Works with Alexa / Works with the Google Assistant
IP Rating: IP Native
Load: 700W incandescent/halogen | 450W LED/CFL | 5.5A EFL | 500VA MLV
Mounting: Standard electrical box
Operating Temperature (Celsius): 0°C to 43°C
Volts: 120
Watts: 450

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: CHINA