



## SMART TRU-UNIVERSAL DIMMER, WI-FI, LIGHT ALMOND

WWRL50LACCV2 | [radiant](#)

### FEATURES & BENEFITS

Take comfort in the convenience of controlling your lights from any smart device to set the exact lighting you need - from anywhere.

The radiant Collection now offers smart switches and outlets with the ability to control lights and set scenes and schedules from any smart device - or just ask Alexa or Google to turn lights on for you. Combining classic design and advanced functionality with simple connection among existing smart home solutions, smart lighting sets the exact lighting you want - when and where you need it.

The radiant® Collection is a step up from standard with simple, classic options in wiring devices, home automation controls and screwless wall plates that complement today's homes.



- Control lights from smart phones and tablets with the Smart Lights app
- Schedule lights on/off automatically, group lights, and create Scenes
- Know your home is secure, even when you're away
- Just ask Amazon Alexa or the Google Assistant to turn lights on
- Out-of-the-box connectivity with OCF certification
- Set the exact lighting level you need
- Installs easily in place of existing switch/dimmer
- Requires neutral wire
- Tru-Universal works with any dimmable 120V bulb or fixture
- Locator light for finding switch the dark
- Available in white, light almond, and nickel colors
- Wall plate included
- Works with existing secure home Wi-Fi (WPA2)
- For multi-location configurations use with Legrand [HMRW dimmer](#)

## SPECIFICATIONS

Conforms to NEMA WD-1 and WD-6, California Title 24 Compliant

FCC ID: A3LCWAM210S

IC ID: 649E-CWAM210S

SSL 7A compliant

Prop65 Compliant

### GENERAL INFO

Color: Light Almond

Available Colors: White, Light Almond, Nickel

Connection Type: Certified IEEE 802.11™ b/g/n Wi-Fi® 2.4GHz radio

Style: Rocker

### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Listing Info: CSA-C22.2 No. 184

CSA Standard: Yes

FCC Standard: Yes

UL Listing No: UL1472

UL Standard: Yes

### CONSTRUCTION INFORMATION

Material 1: Polycarbonate Lexan

### DIMENSIONS

Depth (US): 1.53"

Height (US): 4.17"

Width (US): 1.77"

Weight: 0.30 lbs.

### TECHNICAL INFORMATION

Compatible Power Supplies: Google/Alexa

Humidity: 0-90% relative humidity, non-condensing

Interoperability: OCF 1.3.1. / Works with Alexa / Works with Google Home Assistant

IP Rating: IP Native

Load: 700W incandescent/halogen | 450W LED/CFL | 5.5A EFL | 500VA MLV

Mounting: Standard electrical box

Operating Temperature (Celsius): 0°C to 43°C

Volts: 120

Watts: 450

### BUY AMERICAN ACT COMPLIANCE

Country Of Origin: CHINA