


---

## 880S3 - OMNIBOX SERIES STEEL FLOOR BOX

880S3 | [Wiremold](#)



---

### FEATURES & BENEFITS

This floor box series provides an excellent activation solution for applications where single service is required in open space areas. The floor box is offered in a stamped steel construction, designed to be installed in above-grade concrete floor applications and to meet a wide range of market requirements. This floor box series has many applications, some of which are schools, financial institutions, and commercial office buildings.



- **TopGuard protection.** All cover assemblies for the Omnibox Floor Box Series have TopGuard protection. An integral design which keeps out water, dirt, and debris from the power and communication compartments.
- **Fully adjustable box.** Before and after concrete pour adjustability. Lower installed cost.
- **Concrete-tight stamped steel construction.** Lower cost option for above grade applications.
- **Three-gang configurations, maximum flexibility.** Can remove divider for greater capacity. Supports multiservice applications.
- Boxes and covers have been listed by Underwriters Laboratories Inc. to their standard UL514A, 514C, 514D, and Canadian standard C22.2
- **Flush activation assemblies for carpet and tile.** Aesthetically pleasing assemblies are interchangeable for both cast-iron and stamped steel.
- **Datacom connectivity options.** Accepts industry standard and proprietary devices from a wide range of manufacturers to provide a seamless and aesthetically pleasing interface for voice, data, audio, and video applications at the point-of-use. A wide selection of data and bezel options available for use with Ortronics TracJack and Series II devices.

---

### SPECIFICATIONS


**Conduit Openings:** (5)-1/2" [12.7mm], (11)-3/4" [19.1mm], (6)-1" [25mm]

**Compartment Capacity:** 180 cu in. [2950ml<sup>3</sup>], 58 cu in. [951ml<sup>3</sup>], 68 cu in. [1115ml<sup>3</sup>], 56 cu in. [918ml<sup>3</sup>]

**Adjustment Before Pour:** 1 3/4" [44mm]

**Adjustment After Pour:** 1/2" [12.7mm]

**Knockout Sizes & Locations:**



**GENERAL INFO**

Product Series: Omnibox

Component Type: Boxes

Knockout Size: 1/2"-1"

**CONSTRUCTION INFORMATION**

Installation Location: Above-Grade

**BUY AMERICAN ACT COMPLIANCE**

Country Of Origin: MULTIPLE

Buy American Act Status: Exception

Note: While most parts within this series comply with the BAA's Country of Origin requirements, some do not. For a complete list of all parts and their respective Country of Origin, refer to the "Series Part List-COO" under "Supporting Documents" on the "Resources" tab.