



6AT THREE HOUR FIRE RATED, PREWIRED A/V EVOLUTION™ RECESSED POKE-THRU DEVICE, SURFACE STYLE COVER, BRONZE

6ATC2PAVBZ | [Wiremold](#)

FEATURES & BENEFITS

The Industry's first 3 hour fire rated recessed Poke Thru is here. Designed for retrofit and new construction, Evolution Series 6" Recessed Poke-Thru Devices provide convenient access to power, communications and audio/video services recessed below floor level - providing maximum device protection. With 3 gangs of capacity, you can configure services for the needs of your space. The low-profile metal covers are available in brushed aluminum, satin brass, satin nickel and multiple powder-coated finishes designed to match any space. Evolution Series 6" Poke-Thru Devices are the perfect fit for kiosks, meeting rooms, training rooms, classrooms, healthcare facilities or commercial buildings with open-space architecture. For carpet, tile, wood and laminate concrete floor coverings.

- **Prewired Assembly:** Save on labor with a completely assembled, prewired poke-thru with every power receptacle already installed.
- **Recessed Devices:** All power, communications and A/V devices are recessed below floor level, providing maximum protection and device longevity.
- **"Step-on-it" Installation:** Quick and easy installation without the need for additional fasteners or a second installer.
- **Unique Cover Design:** The cover opens a full 180 degrees with two unique spring-loaded slide egress doors to keep wires, connections and people safe.
- **Multiple Finishes:** Evolution Series Poke-Thru Devices are available in multiple finishes: (BK) black, (GY) gray, (NK) nickel, (BS) brass, (BZ) bronze, (AA) brushed aluminum, (SB) satin brass and (SN) satin nickel to seamlessly match your environment.
- **Ideal for High Foot Traffic Environments:** Satin brass, satin nickel and brushed aluminum finishes offer a more durable, high-end look with a tougher clear powder coat.
- **Surface Style Cover Assemblies:** A surface style cover is for mounting on top of the finished floor surface. The surface cover is designed to be used for carpet, tile, wood, polished concrete, or terrazzo.
- **A/V Ready:** Plates included to accept industry standard communications and A/V devices from most manufacturers including Legrand AVIP, Extron® and more.
- **Plug Load Control Up To 30 Feet:** Tested with Pass & Seymour® Wireless RF receptacles to control plug loads up to a distance of 30 feet when the cover is closed.
- **3 hour fire rating:** Evolution Series Poke-Thru Devices use an intumescent material that maintains the fire rating of any floor for up to 3 hours, the longest of its type.
- **Meets ADA Accessibility Guidelines.** Wide trim flange is designed to meet the ADA Accessibility Guidelines as it pertains to ADA Standard 4.5 which addresses changes in floor and ground surface levels. The poke-thru trim flanges are beveled so the slope is no greater than 1:2 ratio.
- **UL Listed and UL Fire Classified to U.S. and Canadian safety standards.** UL Fire rated for up to 2-hour rated floors maintains the fire classification of the floor.

SPECIFICATIONS

GENERAL INFO

Color: Bronze

DIMENSIONS

Diameter (US): 7-1/4 in

Height (US): 17-3/4 in

Hole Size: 6"

TECHNICAL INFORMATION

Material: Aluminum, Steel, Plastic

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: UNITED STATES OF AMERICA

Buy American Act Status: Buy American Act Compliant

