



8AT PREWIRED CONTROLLED RECEPTACLE EVOLUTION™ RECESSED POKE-THRU DEVICE, SURFACE STYLE COVER, SATIN NICKEL

8ATC2PCRSN | [Wiremold](#)

FEATURES & BENEFITS

Designed for retrofit and new construction, the Controlled Receptacle Evolution Series 8" Recessed Poke-Thru devices provide convenient access to power, communications, and audio/video services recessed below floor level - providing maximum device protection where plugload control is required. With 5 Gangs of capacity, you will be able to configure services for the needs of your space. The low-profile metal covers are available in brushed aluminum, satin brass, satin nickel, and multiple powder-coated finishes designed to match any space. Evolution Series 8" Poke-Thru devices are the perfect fit for kiosks, meeting rooms, training rooms, classrooms, healthcare facilities or commercial buildings with open-space architecture. For carpet, tile, wood and laminate concrete floor coverings.



PRODUCT
ENVIRONMENTAL PROFILE

- **Recessed Devices:** All power, communications and A/V devices are recessed below floor level, providing maximum protection and device longevity.
- **Controlled receptacles installed option:** The only option on the market with two marked receptacles in a 8" poke-thru that also meets Title 24 and ASHRAE Plug Load Control standards helping you meet code, and saving time at installation.
- **Unique Cover Design:** The cover opens a full 180 degrees with two unique spring-loaded slide egress doors to keep wires, connections and people safe.
- **Multiple Finishes:** Evolution Series Poke-Thru Devices are available in multiple finishes, (BK) black, (GY) gray, (NK) nickel, (BS) brass, (BZ) bronze, (AA) brushed aluminum, (SB) satin brass, and (SN) satin nickel to seamlessly match your environment.
- **Ideal for High Foot Traffic Environments:** Satin brass, satin nickel and brushed aluminum finishes offer a more durable, high-end look with a tougher clear powder coat.
- **Surface Style Cover Assemblies:** A surface style cover is for mounting on top of the finished floor surface. The surface cover is designed to be used for carpet, tile, wood, polished concrete, or terrazzo.
- **Open System for Expanded Compatibility:** Accepts industry standard power, communications and A/V devices from most manufacturers including Legrand AVIP, Extron® and more.
- **Includes 3 Gang Opening.** Designed to fit A/V devices, including wall plate style transmitters, like the Crestron DM/TX series, without any additional parts.
- **Meets ADA Accessibility Guidelines.** Wide trim flange is designed to meet the ADA Accessibility Guidelines as it pertains to ADA Standard 4.5 which addresses changes in floor and ground surface levels. The poke-thru trim flanges are beveled so the slope is no greater than 1:2 ratio.
- **UL Listed and UL Fire Classified to U.S. and Canadian safety standards.** UL Fire rated for up to 2-hour rated floors maintains the fire classification of the floor.

SPECIFICATIONS

GENERAL INFO

Color: Satin Brass
Product Series: Evolution
Type: Multi-Service

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes
cULus: Yes

DIMENSIONS

Overall Dimensions (US): 9.25 DIA X 16.75 H
Hole Size: 8"

TECHNICAL INFORMATION

Material: Aluminum, Steel, Plastic

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: UNITED STATES OF AMERICA
Buy American Act Status: Buy American Act Compliant

