



EVOLUTION 6ATC2PAV SERIES RECESSED PREWIRED AUDIO/VIDEO ASSEMBLY WITH SURFACE STYLE COVER

6ATC2PAV | [Wiremold](#)

FEATURES & BENEFITS

For carpet, tile, wood and laminate concrete floor coverings. For use in 6" (152mm) diameter opening. Devices are recessed 3 1/4" (83mm) below floor surface. Die-cast aluminum cover assembly is available in the following powder coated finishes: (BK) black, (GY) gray, (NK) nickel, (BS) brass, (BZ) bronze, (AL) aluminum. INCLUDED: For Side Compartments: One (1) proprietary 20A Duplex Power Receptacle installed, One (1) 682A Device Plate, One (1) 68MAAP Device Plate. For Center Compartment: One (1) 6DEC Mounting Plate, One (1) 6AAP Mounting Plate, One (1) 6MAAP Device Plate. For Bottom Feed Compartment: One (1) 5PTHA 1/2-Gang Pass-Through Housing Assembly, One (1) 1PTHA 1-Gang Pass-Through Housing Assembly, One (1) 575CHA 1/2-Gang 3/4" Conduit Housing Assembly (also includes junction box attached to the 3/4" conduit). NOTE: UL Fire Classified for up to 2-hour rated floors. Receptacles can be wired as a standard or isolated ground device.



- **Aluminium cover assemblies.** The Evolution Series poke-thru design includes all metal die-cast aluminium cover assemblies, with two unique spring-loaded slide egress doors. Available in surface style and flush style in standard finishes of brass, gray, black, nickel, bronze, and aluminium offering a wider range of aesthetic options.
- **Audio/Video unit.** The 6AT Series is available in a dedicated A/V version. Prewired with one 20A duplex receptacle and designed to accept the Extron® Electronics AAP and MAAP Series device lines. The 8AT Series is also compatible with Extron AAP and MAAP devices.
- **Meets ADA Accessibility Guidelines.** Wide trim flange is designed to meet the ADA Accessibility Guidelines as it pertains to ADA Standard 4.5 which addresses changes in floor and ground surface levels. The poke-thru trim flanges are beveled so the slope is no greater than 1:2 ratio.
- **UL Listed and UL Fire Classified to U.S. and Canadian safety standards.** UL Fire rated for up to 2-hour rated floors maintains the fire classification of the floor.
- This product meets the material restrictions of RoHS

SPECIFICATIONS

GENERAL INFO

Available Colors:

6ATC2PAVGY - Gray
6ATC2PAVBK - Black
6ATC2PAVBS - Brass
6ATC2PAVBZ - Bronze
6ATC2PAVNK - Nickel
6ATC2PAVAL - Aluminum

Product Series: Evolution

Type: Multi-Service

Component Type: Full Assemblies

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

DIMENSIONS

Hole Size: 6"

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MULTIPLE

Buy American Act Status: No