



radiant Collection  
radiant® Combination Single Pole Switch and Tamper-Resistant 15A Duplex Self-Test GFCI Receptacles with SafeLock® Protection, Gray  
Part No. 1597SWTTRGRY



A step up from ordinary, this combination device features a compact switch with a tamper-resistant GFCI outlet. Ideal for use with vents in kitchens and baths, the code-compliant outlet self-tests automatically every three seconds to ensure reliable protection ground fault occurrences, and makes it easier to recognize and fix trips right where they happen – no more confusion at the breaker box. Part of the radiant® Collection, it also features sleek, clean lines for a sophisticated look. Made exclusively for use with screwless Wall Plates from the radiant® Collection, sold separately.

## Features & Benefits

- Protects against shock caused by ground-fault occurrences. Unlike breaker alternatives, GFCI Conducts an industry-leading automatic self-test every 3 seconds. If the device ever fails, the indicator light flashes to signal it should be replaced.
- Equipped with proven SafeLock protection feature: if critical components are damaged and protection is lost, power to the receptacle is disconnected.
- Protects children with a patented shutter system that prevents improper insertion of foreign objects, complete with "invisi-shutters" for an invisible effect.
- Installs easily in as little as 10 minutes.
- Features durable, high-impact resistant thermoplastic construction.
- More color options available to fit any style.
- Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection.

## Specifications

### General Info

|                   |                         |                       |  |
|-------------------|-------------------------|-----------------------|--|
| Product Line      | Pass & Seymour          | Color                 | Gray   |
| Country Of Origin | China                   | Number of Receptacles | 2  |
| Features          | Combination             | Outlet Type           | GFCI, Indoor, Residential, Self-Test, Tamper-Resistant |
| Warranty Type     | 1-Year Limited Warranty | Type                  | Outlet, Switch   |

### Dimensions

|                   |         |                  |         |
|-------------------|---------|------------------|---------|
| Product Width US  | 1.73 in | Product Depth US | 1.03 in |
| Product Height US | 4.2 in  |                  |         |

### Listing Agencies / 3rd Party Agencies

|              |     |
|--------------|-----|
| cULus Listed | Yes |
|--------------|-----|

### Technical Information

|                 |                          |                |         |
|-----------------|--------------------------|----------------|---------|
| Number of Gangs | 1                        | Amperage       | 15 A    |
| Number of Poles | Double Pole, Single Pole | Indoor/Outdoor | Indoor  |
| Mounting Type   | Box                      | Voltage        | 125.0 V |