



**Wiremold**  
**Discontinued - 25DTC-E10 - 25DTC Series Blank Steel Tele-Power Express Pole**  
Part No. 25DTC-E10-DG



Two sections of a two-compartment pole (5'4" (1.626m) base + 5' (1.524m) extender) assembles to form a 10' 4" (3.148m) pole. Nominal material thickness .040" (1.0mm). Ivory or gray boot base. Furnished unwired without outlets. Mounting hardware, entrance end plate and ceiling trim plate furnished. An 8" (203mm) cover at top front of pole is removable for making power wiring connections.

## Features & Benefits

Two sections of a two-compartment pole (5'4" (1.626m) base + 5' (1.524m) extender) assembles to form a 10' 4" (3.148m) pole. Nominal material thickness .040" (1.0mm). Ivory or gray boot base. Furnished unwired without outlets. Mounting hardware, entrance end plate and ceiling trim plate furnished. An 8" (203mm) cover at top front of pole is removable for making power wiring connections.

Dual-channel. Allows a single drop point for access to multiple services.

Relocatable. Ready for service in 30 minutes or less. Can be quickly reconfigured or relocated as work space uses and service needs change.

Multiple color options. Available in four aesthetic colors: white, black, ivory, and gray.

Wide selection of standard options. Stocked in a variety of materials, finishes, and heights.

Datacom connectivity options. Accepts industry standard and proprietary devices from a wide range of manufacturers to provide a seamless, aesthetically pleasing interface for voice, data, audio, and video applications at the point of use.

Pole extenders combine quick installation with easy job-site handling. Snap together 5' sections to create a pole or extend the length of your existing 25TP series pole. These new extenders accommodate a variety of ceiling heights, can ship UPS or air freight for quick & reliable delivery.

Custom capabilities. Modify receptacle type and location, change color finish, alter pole heights, add fixture whips and more.

## Specifications

### General Info

Product Line	Wiremold	Replaced by Part Number	25DTC-E10DG, 25DTC-E10DG
UPC Number	786776177169	Country Of Origin	United States

---

Standard

cULus Listed Multioutlet Assemblies: File E15191  
E178348 Guide PVGT, Raceway Fittings: File  
E41751 Guide RJPR, Accessories: File E53857  
Guide RVUR Meets Article 380 & 386 of NEC

---

**Listing Agencies / 3rd Party Agencies**

---

cULus ListingNumber	E15191	cULus Listed	Yes
---------------------	--------	--------------	-----

---

**Additional Information**

---

RoHS Conformant	Yes
-----------------	-----

---