



Wiremold
25DTP Series Steel Tele-Power Pole with Dedicated/Isolated Ground
Part No. 25DTP-4D-DG



25DTP D Series 10' Tele-Power Poles handle all of your needs effortlessly, whether it's power, data, or A/V wiring you need to bring down to the desk, workstation, or cash registers. The vertical drop poles give you the flexibility and capacity to devote both sides of the pole for single service or separate the two channels to provide dual service feeds. This pole comes with two(2) prewired Fed-Spec general grade duplex receptacles, one 20A 125V dedicated/isolated ground duplex receptacle and one 20A 125V standard duplex receptacle. Knockouts provided in removable cover for RJ11/RJ45 and modular furniture communication connectors. All mounting hardware, entrance end plate, and two ceiling trim plates are included.

Features & Benefits

Easy to install

Bring power, data, and A/V services into open space environments quickly & easily. Reduces costs for moves adds and changes.

Dual-channel

Allows a single drop point for access to multiple services.

Multiple color options

available in three aesthetic colors: white, ivory, and gray.

Custom capabilities

Modify receptacle type and location, change color finish, alter pole heights, add fixture whips and more. Affording you more choice in appearance and configuration.

Relocatable

Ready for service in 30 minutes or less. Can be quickly reconfigured or relocated as work space uses and service needs change.

Wide selection of standard options

Stocked in a variety of materials, finishes, heights, and device configurations. Provides what you want, when you need it.

Datacom connectivity options

Accepts industry standard and proprietary devices from a wide range of manufacturers to provide a seamless, aesthetically pleasing interface for voice, data, audio, and video applications at the point of use.

Specifications

General Info

| | | | |
|-------------------|---------------|--------------|--------------|
| Color | Gray | UPC Number | 786776177176 |
| Country Of Origin | United States | Product Line | Wiremold |

| | | | |
|--------------------|------------|----------|--|
| Application Sector | Commercial | Standard | cULus Listed Multioutlet Assemblies: File E15191, E178348 Guide PVGT. Raceway Fittings: File E41751 Guide RJPR. Accessories: File E53857 Guide RVUR Meets Article 380 & 386 of NEC. |
|--------------------|------------|----------|--|

Dimensions

| | | | |
|------------------|-----------|-------------------|---------|
| Product Width US | 2.3125 in | Product Length US | 10.5 FT |
| Product Depth US | 2.25 in | | |

Listing Agencies / 3rd Party Agencies

| | | | |
|--------------|-----|---------------------|--------|
| cULus Listed | Yes | cULus ListingNumber | E15191 |
|--------------|-----|---------------------|--------|

Buy American Act Compliance

| | | | |
|-------|-----|--|--|
| NAFTA | Yes | | |
|-------|-----|--|--|

Additional Information

| | | | |
|-----------------|-----|-------------------------------|-----|
| RoHS Conformant | Yes | Product Environmental Profile | Yes |
|-----------------|-----|-------------------------------|-----|