



Legrand

4AT Prewired Dual Service Controlled Receptacle Evolution™ Poke-Thru Device-Aluminum
Part No. 4ATCP2CRAL

Designed for retrofit and new construction, Evolution Series 4" Poke-Thru devices provide convenient access to power, communications, and audio/video services recessed below floor level - providing maximum device protection. 2-gangs of capacity allow you to configure services for the needs of your space. Evolution Series 4" Poke-Thru devices are the perfect fit for kiosks, training rooms, classrooms, healthcare facilities or commercial buildings with open-space architecture.



Features & Benefits

Prewired assembly: Save on labor with a completely assembled, prewired poke-thru .

Controlled receptacles: The only option on the market with two marked receptacles in a 4" poke-thru that also meets Title 24 Plug Load Control standards.

Recessed devices: All power, communications and A/V devices are recessed below floor level, providing maximum protection and device longevity.

"Step-on-it" installation: Quick and easy installation without the need for additional fasteners or a second installer.

Unique cover design: The cover opens a full 180 degrees with two unique spring-loaded slide egress doors to keep wires, connections and people safe.

Multiple finishes: Evolution Series Poke-Thru Devices are available in multiple finishes, (BK) black, (GY) gray, (NK) nickel, (BS) brass, (BZ) bronze, (AL) aluminum, (AA) brushed aluminum, (SB) satin brass, and (SN) satin nickel to seamlessly match your environment.

Surface style cover assemblies: A surface style cover is for mounting on top of the finished floor surface. The surface cover is designed to be used for carpet, tile, wood, polished concrete, or terrazzo.

Open system for expanded compatibility: Accepts industry standard power, communications and A/V devices from most manufacturers including Legrand AVIP, Extron® and more.

2 hour fire rating: Evolution Series Poke-Thru Devices use an intumescent material that maintains the fire rating of any floor for up to 2 hours.

Meets ADA accessibility guidelines: Wide trim flange is designed to meet the ADA Accessibility Guidelines as it pertains to ADA Standard 4.5 which addresses changes in floor and ground surface levels. The poke-thru trim flanges are beveled so the slope is no greater than 1:2 ratio.

UL Listed and UL fire classified to U.S. and Canadian safety standards: UL Fire rated for up to 2-hour rated floors maintains the fire classification of the floor.

Specifications

General Info

UPC Number 786564090823

Country Of Origin United States

Product Line Wiremold

Application Sector Commercial

Type Poke-Thru

Construction Assembled

Standard cULus Listed Metallic Outlet Boxes: File E2961 Guide QCIT. cULus Listed Nonmetallic Outlet Boxes and Fittings Classified for Fire Resistance: File R8209 Guide CEYY. Meets Article 300.21, 300.22[C] and 314 of NEC.

Number of Knockouts 10

Dimensions

Cubic Capacity	24.5 cu in
----------------	------------

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

cULus ListingNumber	E2961
---------------------	-------

Buy American Act Compliance

NAFTA	Yes
-------	-----

Additional Information

RoHS Conformant	Yes
-----------------	-----

Product Environmental Profile	Yes
-------------------------------	-----

Technical Information

Cable Entry	.75 in
-------------	--------

Number of Outlets	2
-------------------	---
