



Wiremold
4IN UNWIRED FLUSH SYLE ASSEMBLY BZ
Part No. 4ATBZ



Designed for retrofit and new construction, Evolution Series 4" Recessed Poke-Thru devices provide convenient access to power, communications, and audio/video services recessed below floor level - providing maximum device protection. With 2 Gangs of capacity, you will be able to configure services for the needs of your space. The low-profile metal covers are available in brushed aluminum, satin brass, satin nickel, and multiple powder-coated finishes designed to match any space. Evolution Series 4" Poke-Thru devices are the perfect fit for kiosks, training rooms, classrooms, healthcare facilities or commercial buildings with open-space architecture.

Features & Benefits

Prewired assembly: Save on labor with a completely assembled, prewired poke-thru with every power receptacle already installed.

Recessed devices: All power devices are recessed below floor level, providing maximum protection and device longevity.

Step-on-it installation: Quick and easy installation without the need for additional fasteners or a second installer.

Unique cover design: The cover opens a full 180 degrees with two unique spring-loaded slide egress doors to keep wires, connections and people safe

Multiple finishes: Evolution Series Poke-Thru Devices are available in multiple finishes, (BK) black, (GY) gray, (BZ) bronze, (AL) aluminum, (AA) brushed aluminum, (SB) satin brass, and (SN) satin nickel to seamlessly match your environment.

Surface style cover assemblies: A surface style cover is for mounting on top of the finished floor surface. The surface cover is designed to be used for carpet, tile, wood, polished concrete, or terrazzo.

3 hour fire rating: Evolution Series Poke-Thru Devices use an intumescent material that maintains the fire rating of any floor for up to 2 hours.

Wide trim flange is designed to meet the ADA Accessibility Guidelines as it pertains to ADA Standard 4.5 which addresses changes in floor and ground surface levels. The poke-thru trim flanges are beveled so the slope is no greater than 1:2 ratio.

UL Listed and UL fire classified to U.S. and Canadian safety standards: UL Fire rated for up to 2-hour rated floors maintains the fire classification of the floor.

Specifications

General Info

Product Line	Wiremold	Color	Bronze
UPC Number	786564104957	Country Of Origin	United States
Receptacle Type	Straight Blade	Features	Recessed

Cover Style	Flush	Number of Knockouts	10
Application Sector	Commercial, Education, Healthcare, Hospitality	Standard	UL Fire Classified, cULus, NEC
Warranty Type	1-Year from Installation or 2-Years from Day of Sale	Type	Poke-Thru
Dimensions			
Product Width US	5.5 in	Product Weight US	5.75 lb
Product Length US	5.5 in	Cubic Capacity	25 in ³
Core Hole Size	4 in	Knockout Size	1-1/2 in, 3/4 in
Listing Agencies / 3rd Party Agencies			
cULus Listed	Yes		
Additional Information			
Product Has Potential to Contribute to LEED	Yes	Product Environmental Profile	Yes
Technical Information			
Floor Type	Carpet, Concrete, Tile, Wood	Is Tamper-Resistant	No
Is Pre-Wired	No	Fire Rating	2 hr
Amperage	20 A	Current Rating	20 A
NEMA Configuration Code	5-20R	Voltage	125.0 V