



Wiremold 4FFATC15 Flush Furniture Feed Poke-Thru Assembly, Nickel Part No. 4FFATC15NK



Complete with one-piece finish flange and conduit assembly. Conduit assembly consists of one 3/4inch trade size conduit and one 1 1/2inch trade size conduit. Finish cover flange provided with one 3/4inch trade size screw plug opening and one 1 1/2inch trade size screw plug opening. Covers available in painted black (BK), gray (GY), brass (BS), bronze (BZ), and brushed aluminum (AL). NOTE: Assembled with scrub water gasket. For use on tile, wood or carpet floors.

Features & Benefits

Integral design component that prevents water, dirt and debris from entering power and communication compartments.

Provides one 3/4" opening for power and one 1 1/2" opening for communication cabling. Provides largest dual service capacity for furniture feed applications in the industry. UL Listed for both power and communication furniture feed applications.

Suitable for use in air handling spaces in accordance with Sec. 300-22 (C) of the National Electrical Code.

UL Listed and UL Fire Classified to U.S. and Canadian safety standards for tile and terrazzo. Includes the new UL requirements under UL514A and UL514C for the scrub water exclusion test for carpet and wood floors..

Step-on-it installation. Quick and easy installation without the need for additional fasteners or the need for a second installer.

Whenever you see the TopGuard protection icon on any Wiremold product, you'll know it meets and exceeds UL scrub water exclusion requirements for tile and carper floors.

Specifications

General Info

Product Line	Wiremold	Color	Nickel
UPC Number	786564085317	Country Of Origin	Mexico
Cover Style	Flush, Furniture Feed	Number of Knockouts	2
Application Sector	Commercial, Education, Healthcare, Hospitality	Standard	UL Fire Classified, cULus, NEC
Warranty Type	1-Year from Installation or 2-Years from Day of Sale	Type	Poke-Thru

Dimensions

Product Width US	8.0 in	Product Weight US	6.0 lb
Product Volume US	1024.0 cu in	Product Depth US	16.0 in
Product Height US	8.0 in	Cubic Capacity	24.5 in ³
Core Hole Size	4 in	Knockout Size	1-1/2 in, 3/4 in

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E2961	cULus Listed	Yes
---------------------	-------	--------------	-----

Trade Programs

USMCA	Yes
-------	-----

Additional Information

RoHS Compliant	Yes	Product Environmental Profile	Yes
----------------	-----	-------------------------------	-----

Technical Information

Floor Type	Carpet, Concrete, Tile, Wood	Fire Rating	2 hr
------------	------------------------------	-------------	------
