




Wiremold  
Evolution 6AT2P Series Recessed Prewired Assembly with Flush Style Cover  
Part No. 6AT2PBZ



Designed for retrofit and new construction, Evolution Series 6inch Poke-Thru devices provide convenient access to power, communications, and audio/video services recessed below floor level - providing maximum device protection. With 3-gangs of capacity that allow you to configure services for the needs of your space, services can be placed in any location within the unit. The low-profile durable metal covers are available in six powder-coated finishes and three durable finishes, designed to match any space. The cover also features sliding doors that allow cables to neatly egress from the unit, protecting cables while reducing tripping hazards. Evolution Series 6inch Poke-Thru devices are the perfect fit for meeting and training rooms, classrooms, healthcare facilities or commercial buildings with open-space architecture.

## Features & Benefits

- Prewired assembly:** Save on labor with a completely assembled, prewired poke-thru with every power receptacle already installed.
- Step-on-it installation:** Quick and easy installation without the need for additional fasteners or a second installer.
- Evolution Series Poke-Thru Devices** are available in multiple finishes, (BK) black, (GY) gray, (NK) nickel, (BS) brass, (BZ) bronze, (AL) aluminum, (AA) brushed aluminum, (SB) satin brass, (SN) satin nickel to seamlessly match your environment.
- Open system for expanded compatibility:** Accepts industry standard power, communications and A/V devices from most manufacturers including Legrand AVIP, Extron® and more.
- 2 hour fire rating:** Evolution Series Poke-Thru Devices use an intumescent material that maintains the fire rating of any floor for up to 2 hours.
- Wide trim flange** is designed to meet the ADA Accessibility Guidelines as it pertains to ADA Standard 9
- UL Listed and UL fire classified** to U.S. and Canadian safety standards: UL Fire rated for up to 2-hour rated floors maintains the fire classification of the floor.
- All power, communications and A/V devices are recessed below floor level, providing maximum protection and device longevity.
- The cover opens a full 180 degrees with two unique spring-loaded slide egress doors to keep wires, connections and people safe.
- A surface style cover is for mounting on top of the finished floor surface. The surface cover is designed to be used for carpet, tile, wood, polished concrete, or terrazzo.
- Plug load control up to 30 feet: Tested with Pass & Seymour® Wireless RF receptacles to control plug loads up to a distance of 30 feet when the cover is closed.
- Meets ADA accessibility guidelines.
- The poke-thru trim flanges are beveled so the slope is no greater than 1:2 ratio

## Specifications

### General Info

Product Line	Wiremold	Color	Bronze
UPC Number	786564088905	Country Of Origin	United States

Construction	Assembled	Features	Recessed
Cover Style	Flush	Application Sector	Commercial, Education, Healthcare, Hospitality
Standard	UL Fire Classified, cULus, NEC	Warranty Type	1-Year from Installation or 2-Years from Day of Sale
Type	Poke-Thru		
Dimensions			
Product Width US	7.25 in	Product Weight US	9.35 lb
Product Height US	16.25 in	Cubic Capacity	24 in <sup>3</sup>
Core Hole Size	6 in	Knockout Size	3/4 in
Listing Agencies / 3rd Party Agencies			
cULus ListingNumber	E2961	cULus Listed	Yes
Additional Information			
RoHS Compliant	Yes		
Technical Information			
Floor Type	Carpet, Concrete, Tile, Wood	Is Pre-Wired	Yes
Service Capacity	Dual	Fire Rating	2 hr
Cable Entry	CONDUIT		