



Wiremold 3-Hour Fire Classified 6" Recessed Prewired Surface Style Poke-Thru Assembly Part No. 6ATC2PBK3H



Designed for retrofit and new construction, Evolution Series 6" Recessed Poke-Thru devices provide convenient access to power, communications, and audio/video services recessed below floor level - providing maximum device protection. With 3 Gangs of capacity, you will be able to configure services for the needs of your space. The low-profile metal covers are available in brushed aluminum, satin brass, satin nickel, and multiple powder-coated finishes designed to match any space. Evolution Series 6" Poke-Thru devices are the perfect fit for kiosks, meeting rooms, training rooms, classrooms, healthcare facilities or commercial buildings with open-space architecture. For carpet, tile, wood and laminate concrete floor coverings.

Features & Benefits

Prewired assembly: Save on labor with a completely assembled, prewired poke-thru with every power receptacle already installed.

Step-on-it installation: Quick and easy installation without the need for additional fasteners or a second installer.

Multiple finishes: Evolution Series Poke-Thru Devices are available in multiple finishes: (BK) black, (GY) gray, (BZ) bronze, (AA) brushed aluminum, (SB) satin brass and (SN) satin nickel to seamlessly match your environment.

Open system for expanded compatibility: Accepts industry standard power, communications and A/V devices from most manufacturers including Legrand AVIP, Extron® and more.

3 hour fire rating: Evolution Series Poke-Thru Devices use an intumescent material that maintains the fire rating of any floor for up to 3 hours.

Recessed devices: All power, communications and A/V devices are recessed below floor level, providing maximum protection and device longevity.

Unique cover design: The cover opens a full 180 degrees with two unique spring-loaded slide egress doors to keep wires, connections and people safe.

Surface style cover assemblies: A surface style cover is for mounting on top of the finished floor surface. The surface cover is designed to be used for carpet, tile, wood, polished concrete, or terrazzo.

Plug load control up to 30 feet: Tested with Pass & Seymour® Wireless RF receptacles to control plug loads up to a distance of 30 feet when the cover is closed.

Wide trim flange is designed to meet the ADA Accessibility Guidelines as it pertains to ADA Standard 4.5 which addresses changes in floor and ground surface levels. The poke-thru trim flanges are beveled so the slope is no greater than 1:2 ratio.

Specifications

General Info

Product Line	Wiremold	Color	Black
UPC Number	786564103509	Country Of Origin	United States
Features	Recessed	Cover Style	Surface
Application Sector	Commercial, Education, Healthcare, Hospitality	Standard	UL Fire Classified, cULus, NEC

Warranty Type	1-Year from Installation or 2-Years from Day of Sale	Type	Poke-Thru
---------------	--	------	-----------

Dimensions

Product Weight US	10.47 lb	Core Hole Size	6 in
-------------------	----------	----------------	------

Knockout Size	3/4 in
---------------	--------

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E2961	cULus Listed	Yes
---------------------	-------	--------------	-----

Additional Information

Product Environmental Profile	Yes
-------------------------------	-----

Technical Information

Floor Type	Carpet, Concrete, Polished Concrete, Terrazzo, Tile, Wood	Is Pre-Wired	Yes
------------	---	--------------	-----

Service Capacity	Dual	Fire Rating	3 hr
------------------	------	-------------	------
