



Legrand

6AT Prewired Evolution™ Poke Thru Device, Surface Style Cover, Nickel
Part No. 6ATC2PNK



Designed for retrofit and new construction, Evolution Series 6" Recessed Poke-Thru devices provide convenient access to power, communications, and audio/video services recessed below floor level - providing maximum device protection. With 3 Gangs of capacity, you will be able to configure services for the needs of your space. The low-profile metal covers are available in brushed aluminum, satin brass, satin nickel, and multiple powder-coated finishes designed to match any space. Evolution Series 6" Poke-Thru devices are the perfect fit for kiosks, meeting rooms, training rooms, classrooms, healthcare facilities or commercial buildings with open-space architecture. For carpet, tile, wood and laminate concrete floor coverings.

Features & Benefits

Prewired assembly: Save on labor with a completely assembled, prewired poke-thru with every power receptacle already installed.

Recessed devices: All power, communications and A/V devices are recessed below floor level, providing maximum protection and device longevity.

"Step-on-it" installation: Quick and easy installation without the need for additional fasteners or a second installer.

Unique cover design: The cover opens a full 180 degrees with two unique spring-loaded slide egress doors to keep wires, connections and people safe.

Multiple finishes: Evolution Series Poke-Thru Devices are available in multiple finishes, [BK] black, [GY] gray, [NK] nickel, [BS] brass, [BZ] bronze, [AL] aluminum, [AA] brushed aluminum, [SB] satin brass, [SN] satin nickel to seamlessly match your environment.

Surface style cover assemblies: A surface style cover is for mounting on top of the finished floor surface. The surface cover is designed to be used for carpet, tile, wood, polished concrete, or terrazzo.

Open system for expanded compatibility: Accepts industry standard power, communications and A/V devices from most manufacturers including Legrand AVIP, Extron® and more.

Plug load control up to 30 feet: Tested with Pass & Seymour® Wireless RF receptacles to control plug loads up to a distance of 30 feet when the cover is closed.

2 hour fire rating: Evolution Series Poke-Thru Devices use an intumescent material that maintains the fire rating of any floor for up to 2 hours.

Meets ADA accessibility guidelines: Wide trim flange is designed to meet the ADA Accessibility Guidelines as it pertains to ADA Standard 4.5 which addresses changes in floor and ground surface levels. The poke-thru trim flanges are beveled so the slope is no greater than 1:2 ratio.

UL Listed and UL fire classified to U.S. and Canadian safety standards: UL Fire rated for up to 2-hour rated floors maintains the fire classification of the floor.

Specifications

General Info

UPC Number 786564088783

Country Of Origin United States

Product Line Wiremold

Application Sector Commercial

Type Poke-Thru

Standard cULus Listed Metallic Outlet Boxes: File E2961 Guide QCIT. cULus Listed Nonmetallic Outlet Boxes & Fittings Classified for Fire Resistance: File R8209 Guide CEYY. Meets Article 300.21, 300.22[C] & 314 of NEC.

Number of Knockouts 2

Dimensions

Product Volume US 854.14

Product Width US 7.25

Product Height US	7.25
-------------------	------

Product Weight US	9.44
-------------------	------

Product Depth US	16.25
------------------	-------

Core Hole Size	6 in
----------------	------

Cubic Capacity	24.5 cu in
----------------	------------

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

cULus ListingNumber	E2961
---------------------	-------

Buy American Act Compliance

NAFTA	Yes
-------	-----

Additional Information

RoHS Conformant	Yes
-----------------	-----

Product Environmental Profile	Yes
-------------------------------	-----

Technical Information

Number of Outlets	4
-------------------	---
