



**Wiremold**  
**861QTC Series Wood Floor Box Assembly**  
Part No. 861QTCBK



Complete with prewired 15A quad receptacle can be wired as standard or isolated ground. Flush poke-thru-style flanges available in a variety of colors/finishes. Slide covers match painted flange colors. Aluminum and brass covers shipped with black slide covers. Brass flange also available with nonmetallic brass-color slide holder. Die-cast aluminum construction with three 1/2" trade size knockouts: two on the sides and one on the bottom. 18 cu. in. (295 cu.cm) capacity. Requires a 4" (102mm) diameter hole and overall floor depth of 1" (25mm). Assembled with scrub water gasket. For use on tile, wood, or carpet floors.

## Features & Benefits

Complete with prewired 15A quad receptacle can be wired as standard or isolated ground.

Slide covers match painted flange colors

Brass flange also available with nonmetallic brass-color slide holder

Requires a 4" (102mm) diameter hole and overall floor depth of 1" (25mm). Assembled with scrub water gasket. For use on tile, wood, or carpet floors.

Flush poke-thru-style flanges available in a variety of colors/finishes

Aluminum and brass covers shipped with black slide covers

Requires a 4" (102mm) diameter hole and overall floor depth of 1" (25mm). Assembled with scrub water gasket. For use on tile, wood, or carpet floors.

## Specifications

### General Info

Product Line	Wiremold	Finish	Painted
UPC Number	786564013266	Country Of Origin	Mexico
Construction	Assembled	Cover Style	Flush
Number of Knockouts	3	Cover Material	Die-Cast Aluminum
Application Sector	Commercial	Standard	cULus Listed Metallic Outlet Boxes: File E2961 Guide QCIT Meets Article 314.27(C) of NEC.
Warranty Type	1-Year from Installation or 2-Years from Day of Sale	Type	Floor Box

---

## Dimensions

---

Product Weight US	2.5 lb	Cubic Capacity	18 in <sup>3</sup>
-------------------	--------	----------------	--------------------

---

Knockout Size	1/2 in
---------------	--------

---

## Listing Agencies / 3rd Party Agencies

---

cULus ListingNumber	E2961	cULus Listed	Yes
---------------------	-------	--------------	-----

---

## Trade Programs

---

USMCA	Yes
-------	-----

---

## Additional Information

---

RoHS Compliant	Yes
----------------	-----

---

## Technical Information

---

Floor Type	Raised, Wood	Service Capacity	Single
------------	--------------	------------------	--------

---

Minimum Floor Depth	1 in	Amperage	15 A
---------------------	------	----------	------

---

Box Capacity	1 Gang	Cable Entry	knockout
--------------	--------	-------------	----------

---

Number of Outlets	4
-------------------	---

---