



Designed for retrofit and new construction, Evolution Series 8" Recessed Poke-Thru devices provide convenient access to power, communications, and audio/video services recessed below floor level - providing maximum device protection. With 5 Gangs of capacity, you will be able to configure services for the needs of your space. Evolution Series 8" Poke-Thru devices are the perfect fit for kiosks, meeting rooms, training rooms, classrooms, healthcare facilities or commercial buildings with open-space architecture. For carpet, tile, wood and laminate concrete floor coverings.

Features & Benefits

Prewired assembly: Save on labor with a completely assembled, prewired poke-thru with every power receptacle already installed.

"Step-on-it" installation: Quick and easy installation without the need for additional fasteners or a second installer.

Includes 3-gang opening: Designed to fit A/V devices, including wall plate style transmitters, like the Crestron DM/TX series, without any additional parts.

2 hour fire rating: Evolution Series Poke-Thru Devices use an intumescent material that maintains the fire rating of any floor for up to 2 hours.

The poke-thru trim flanges are beveled so the slope is no greater than 1:2 ratio. UL Listed and UL fire classified to U.S. and Canadian safety standards: UL Fire rated for up to 2-hour rated floors maintains the fire classification of the floor.

Recessed devices: All power, communications and A/V devices are recessed below floor level, providing maximum protection and device longevity.

Open system for expanded compatibility: Accepts industry standard power, communications and A/V devices from most manufacturers including Legrand AVIP, Extron® and more.

Plug load control up to 30 feet: Tested with Pass & Seymour® Wireless RF receptacles to control plug loads up to a distance of 30 feet when the cover is closed.

Meets ADA accessibility guidelines: Wide trim flange is designed to meet the ADA Accessibility Guidelines as it pertains to ADA Standard 4.5 which addresses changes in floor and ground surface levels.

Specifications

General Info

Product Line	Wiremold	Color	Silver
UPC Number	786564070153	Country Of Origin	United States
Features	Recessed	Number of Knockouts	2

Application Sector	Commercial, Education, Healthcare, Hospitality	Standard	UL Fire Classified, cULus, NEC
--------------------	--	----------	--------------------------------

Warranty Type	1-Year from Installation or 2-Years from Day of Sale	Type	Poke-Thru
---------------	--	------	-----------

Dimensions

Product Width US	9.0 in	Product Weight US	9.0 lb
------------------	--------	-------------------	--------

Product Volume US	1316.25 cu in	Product Depth US	16.25 in
-------------------	---------------	------------------	----------

Product Height US	9.0 in	Cubic Capacity	24.5 in ³
-------------------	--------	----------------	----------------------

Core Hole Size	8 in	Knockout Size	1/2 in, 3/4 in
----------------	------	---------------	----------------

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E2961	cULus Listed	Yes
---------------------	-------	--------------	-----

Trade Programs

USMCA	Yes
-------	-----

Additional Information

RoHS Compliant	Yes	Product Environmental Profile	Yes
----------------	-----	-------------------------------	-----

Technical Information

Floor Type	Concrete	Is Pre-Wired	Yes
------------	----------	--------------	-----

Service Capacity	Dual	Fire Rating	2 hr
------------------	------	-------------	------

Cable Entry	Knockouts & Pass Through	Number of Outlets	4
-------------	--------------------------	-------------------	---
