



This box has a 5" (127mm) depth design and can accommodate four duplex power receptacles on one side. Power plate with duplex knockouts included with box. The communication plate will accept at least three communication adapters for up to 18 ports of activation. Lids rotate 180° for easy orientation. Gray lids are diecast zinc construction. NOTE: For custom options, consult factory. All boxes are sold with one power plate: 4" (102mm) deep boxes have plate with two power duplex receptacle KOs, 5" (127mm) deep boxes have plate with four power duplex receptacle KOs. All communication plates sold separately.

Features & Benefits

This box has a 5" (127mm) depth design and can accommodate four duplex power receptacles on one side. Power plate with duplex knockouts included with box.

All boxes are sold with one power plate: 4" (102mm) deep boxes have plate with two power duplex receptacle KOs, 5" (127mm) deep boxes have plate with four power duplex receptacle KOs.

The communication plate will accept at least three communication adapters for up to 18 ports of activation. Lids rotate 180° for easy orientation. Gray lids are diecast zinc construction.

NOTE: For custom options, consult factory. All communication plates sold separately.

Specifications

General Info

Product Line	Wiremold	UPC Number	786564521358
Country Of Origin	United States	Construction	Assembled
Cover Material	Die-Cast Zinc	Application Sector	Commercial
Standard	UL Listed Classified Raised Floor Box: File E2961 Guide QCIT, UL Listed Classified Raised Floor Box (prewired): File E51105 Guide QQVX, Meets Article 314 of NEC. Meets Article 12 2500 of CEC.	Warranty Type	1-Year from Installation or 2-Years from Day of Sale
Type	Floor Box		

Dimensions

Product Width US	8.0 in	Product Weight US	12.3 lb
------------------	--------	-------------------	---------

Product Depth US	5.0 in	Product Length US	8.0 in
------------------	--------	-------------------	--------

Knockout Size	1/2 in, 3/4 in
---------------	----------------

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E2961	cULus Listed	Yes
---------------------	-------	--------------	-----

Trade Programs

USMCA	Yes
-------	-----

Additional Information

RoHS Compliant	Yes
----------------	-----

Technical Information

Floor Type	Raised	Service Capacity	Single
------------	--------	------------------	--------

Minimum Floor Depth	5 in	Box Capacity	4 Gangs
---------------------	------	--------------	---------

Cable Entry	Through Floor	Box Type	Recessed
-------------	---------------	----------	----------

Depth Behind Device Plates	2 in
----------------------------	------
