



Combine Wi-Fi Lighting Control with sleek touch technology and the option to dim, for truly contemporary control. The Touch Wi-Fi Ready Master Dimmer is a programmable light switch and dimmer combination that pairs with the adore Hub to create a smart Wi-Fi Lighting Control System in your home. (For 3-way, or multi-way applications, use one master device with additional remote devices.) Turn lights on/off, or adjust their brightness, with just the touch of a finger. And, create custom lighting settings to control lights from your smartphone or tablet via the Legrand Lighting Control app. Also compatible with Amazon Alexa and Google Home. Made exclusively for use with screwless Wall Plates from the adore® Collection, sold separately.

Features & Benefits

Installs in 25 minutes or less, fitting into an existing electrical box and wiring directly to the light. For use with incandescent/halogen bulbs.

Compatible with iOS and Android devices for app-based control, simply download the free Legrand Lighting Control app.

Part of the adore Wi-Fi Lighting Control System, this device requires the adore Hub to operate.

Complete the look with a stunning, screwless adore® Wall Plate, not included. Available in a range of contemporary colors and finishes. Coordinate with other designer switches & outlets.

Pair with a Touch Wi-Fi Ready Remote Dimmer to allow for 3-way control. Simply follow the provided instructions after installing to pair with the Master Dimmer.

Also compatible with Amazon Alexa and Google Home, and even integrates into advanced home automation systems.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

Specifications

General Info

Product Line	Pass & Seymour	Color	White
UPC Number	804428065616	Country Of Origin	United States
Features	Indicator Lights, Smart Lighting	Switch Type	Touch
Number of Switches	1	Works With	Amazon Alexa, Google Assistant, Radio Frequency
Device Front Face Size	Full-Size	Device Backbody Size	Plus-Size
Application Sector	Residential	Standard	cULus, FCC, UL 1472

Warranty Type	2-Year Limited Warranty
---------------	-------------------------

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes	FCC Compliant	Yes
--------------	-----	---------------	-----

Additional Information

RoHS Compliant	Yes
----------------	-----

Technical Information

Actuator	Touch	Number of Gangs	1
----------	-------	-----------------	---

Amperage	5.5 A	Bulb Compatibility	Halogen, Incandescent
----------	-------	--------------------	-----------------------

Number of Poles	3-Way, Multi-Location, Single Pole	Requires Neutral Wire	Yes
-----------------	------------------------------------	-----------------------	-----

Wattage	600 W	Mounting Type	Box
---------	-------	---------------	-----

Connection Type	Internal Pressure Plates	Load	Incandescent
-----------------	--------------------------	------	--------------

Environmental Conditions	0 to 80% (relative humidity, non-condensing)
--------------------------	--
