




## adore Collection

Discontinued - adore® Touch™ Wi-Fi Ready Master Tru-Universal Dimmer, Magnesium

Part No. ADTH700RMTUM1



Combine Wi-Fi Lighting Control with sleek touch technology and the option to dim, for truly contemporary control. The Touch Wi-Fi Ready Master Dimmer is a programmable light switch and dimmer combination that pairs with the adore Hub to create a smart Wi-Fi Lighting Control System in your home. (For 3-way, or multi-way applications, use one master device with additional remote devices.) Turn lights on/off, or adjust their brightness, with just the touch of a finger. And, create custom lighting settings to control lights from your smartphone or tablet via the Legrand Lighting Control app. Also compatible with Amazon Alexa and Google Home. A Tru-Universal Dimmer, it also works with virtually any 120V dimmable bulb or fixture. Made exclusively for use with screwless Wall Plates from the adore® Collection, sold separately.

## Features & Benefits

Installs in 25 minutes or less, fitting into an existing electrical box and wiring directly to the light.

Self-calibrates when you select your fixture's lighting type, automatically setting the appropriate minimum voltage to eliminate flicker and poor performance.

Compatible with iOS and Android devices for app-based control, simply download the free Legrand Lighting Control app.

Part of the adore Wi-Fi Lighting Control System, this device requires the adore Hub to operate.

Complete the look with a stunning, screwless adore® Wall Plate, not included. Available in a range of contemporary colors and finishes. Coordinate with other designer switches & outlets.

Works with virtually any 120V dimmable bulb or fixture.

Pair with a Touch Wi-Fi Ready Remote Dimmer for 3-way control. Simply follow the provided instructions after installing to pair with the Master Dimmer.

Also compatible with Amazon Alexa and Google Home, and even integrates into advanced home automation systems.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Magnesium
UPC Number	804428067733	Country Of Origin	United States
Features	Smart Lighting, Indicator Lights	Switch Type	Touch
Number of Switches	1	Works With	Amazon Alexa, Google Assistant, Radio Frequency

---

Application Sector	Residential	Standard	cULus, FCC, UL 1472
--------------------	-------------	----------	---------------------

---

### Listing Agencies / 3rd Party Agencies

---

cULus Listed	Yes
--------------	-----

---

### Additional Information

---

RoHS Conformant	Yes
-----------------	-----

---

### Technical Information

---

Actuator	Touch	Frequency Rating	900 M (RF) Hz
----------	-------	------------------	---------------

---

Number of Gangs	1	Amperage	5.5 A
-----------------	---	----------	-------

---

Bulb Compatibility	Universal, LED, Incandescent, Halogen, Fluorescent, CFL, Xenon, HID	Number of Poles	Single Pole, 3-Way, Multi-Location
--------------------	---	-----------------	------------------------------------

---

Wattage	700 W	Mounting Type	Box
---------	-------	---------------	-----

---

Voltage	120 V	Connection Type	Internal Pressure Plates
---------	-------	-----------------	--------------------------

---

Load	Incandescent, Halogen, MLV, Fluorescent, and ELV, CFL, and LED bulbs	Environmental Conditions	0 to 80 (relative humidity, non-condensing)
------	--	--------------------------	---

---