



The whisper-control modern dimmer switches from the adorne Collection allow you to control lights with a soft, fluid motion. Integral silver contacts provide long-lasting performance. A self-calibrating Tru-Universal Dimmer, this dimmer switch works with virtually any 120V dimmable bulb or fixture (excludes 0-10V).

This dimmer\* features enduring Microban® antimicrobial technology that works to reduce the growth of bacteria, around the clock, for the lifespan of the product.

\* Existing inventory of switches, dimmers and plastic wall plates from the adorne® Collection at some partner locations may not yet include Microban® protection. To confirm that a specific Legrand product is protected with Microban®, check that the exterior of the product packaging includes a green dot or a "Protected with Microban" label.

Made exclusively for use with screwless Wall Plates from the adorne® Collection, sold separately.

No antimicrobial efficacy claims are being made or are valid with respect to products sold in Canada.

## Features & Benefits

Helps fight the growth of stain and odor-causing bacteria through the invisible and continuous product protection of Microban® antimicrobial technology

Installs in 15 minutes or less, fitting into an existing electrical box; neutral wire required.

Works with virtually any 120V dimmable bulb or fixture (excludes 0-10V).

Usable in both single-pole and 3-way applications.

For complete installation, device must be paired with an adorne® screwless Wall Plate (not included). Available in a range of contemporary colors and stunning finishes.

Control lights with a fluid, whisper-soft toggle motion to turn on/off, or use the smooth slider to dim or brighten to your preferred light level.

Self-calibrates when you select your fixture's lighting type, automatically setting the appropriate minimum voltage to eliminate flicker and poor performance.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

## Specifications

### General Info

Product Line	Pass & Seymour	Color	White
Finish	Gloss	UPC Number	785007133929

Country Of Origin	China	Features	Antimicrobial Protection, Auto-Calibration (Trim), High-End Trim (Dim Range), Locator Light, Low-End Trim (Dim Range)
Switch Type	Single Pole 3-Way, Slider, Whisper	Number of Switches	1
Device Front Face Size	Full-Size	Device Backbody Size	Plus-Size
Application Sector	Commercial, Hospitality, Residential	Warranty Type	Limited Lifetime Warranty
Type	Dimmer		
<b>Dimensions</b>			
Product Width US	1.77 in	Product Depth US	1.2 in
Product Height US	4.19 in		
<b>Technical Information</b>			
Preset	Yes	Load Rating	120V 4.5A 450W (CFL), 120V 4.5A 450W (LED), 120V 5.5A (EFL), 120V 500VA (MLV), 120V 700W (ELV), 120V 700W (Halogen), 120V 700W (Incandescent)
Dimming Compatibility	Forward or Reverse Selectable Phase	Frequency Rating	60 Hz
Number of Poles	Single Pole 3-Way	Wire Size	#14 - #10 AWG
Requires Neutral Wire	Yes	Indoor/Outdoor	Indoor
Mounting Type	Wall Box	Wire Connection Type	Flying Leads
Voltage	120 VAC	Load Type	CFL, Fluorescent, Halogen, Incandescent, LED